


Thick Film Resistor Networks, Dual-In-Line, Medium Body, Small Outline, Molded DIP, Surface Mount



FEATURES

- Isolated, bussed and dual terminator schematics available
- 14, 16, or 20 terminal package
- Molded case construction
- Thick film resistive elements
- Reflow solderable
- Compatible with automatic surface mounting equipment
- Reduces total assembly costs
- For wave flow soldering contact factory
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912



Available


RoHS*
Available

Note

* This datasheet provides information about parts that are RoHS-compliant and / or parts that are non RoHS-compliant. For example, parts with lead (Pb) terminations are not RoHS-compliant. Please see the information / tables in this datasheet for details

STANDARD ELECTRICAL SPECIFICATIONS

GLOBAL MODEL	CIRCUIT	POWER RATING ELEMENT $P_{70^{\circ}\text{C}}$ W	POWER RATING PACKAGE $P_{70^{\circ}\text{C}}$ W	TOLERANCE $\pm \%$	RESISTANCE RANGE Ω	MAXIMUM WORKING VOLTAGE V_{DC}	TEMPERATURE COEFFICIENT $\pm \text{ppm}/^{\circ}\text{C}$
SOMC14	01	0.08	1.05	1, 2, 5	10 to 1M	50	100
	03	0.16	1.125	1, 2, 5	10 to 1M	50	100
	05	0.08	1.05	1, 2, 5	10 to 1M	50	100
SOMC16	01	0.08	1.20	1, 2, 5	10 to 1M	50	100
	03	0.16	1.28	1, 2, 5	10 to 1M	50	100
	05	0.08	1.20	1, 2, 5	10 to 1M	50	100
SOMC20	01	0.08	1.52	1, 2, 5	10 to 1M	50	100
	03	0.16	1.60	1, 2, 5	10 to 1M	50	100
	05	0.08	1.52	1, 2, 5	10 to 1M	50	100

Notes

- DSCC has created series of drawings to support the need for a surface mount gull wing resistor network product. Vishay Dale is listed as a resource on this drawing as follows:

DSCC DRAWING NUMBER	VISHAY DALE MODEL	CIRCUIT	POWER RATING ELEMENT $P_{70^{\circ}\text{C}}$ W	POWER RATING PACKAGE $P_{70^{\circ}\text{C}}$ W	RESISTANCE RANGE Ω	TOLERANCE $\pm \%$	TEMPERATURE COEFFICIENT $(0^{\circ}\text{C to } 70^{\circ}\text{C}) \pm \text{ppm}/^{\circ}\text{C}$	MAXIMUM WORKING VOLTAGE V_{DC}
87012	SOMC1601..16	01 (B)	0.08	1.20	10 to 2.2M	1, 2, 5	100, 300	50
	SOMC1603..17	03 (A)	0.16					
	SOMC1605..48	05 (J)	0.08					
87013	SOMC1401..6	01 (B)	0.08	1.00	10 to 2.2M	1, 2, 5	100, 300	50
	SOMC1403..13	03 (A)	0.16					
	SOMC1405..22	05 (J)	0.08					

These drawings can be viewed at: www.landandmaritime.dla.mil/Programs/MilSpec/ListDwgs.aspx?DocTYPE=DSCCdwg.

- Power rating depends on the max. temperature at the solder point, the component placement density and the substrate material
- Jumper: 0 Ω -resistor on request (100 m Ω)
- Packaging: According to EIA; see appropriate catalog or web page

(1) Temperature range: -55 $^{\circ}\text{C}$ to +125 $^{\circ}\text{C}$

(2) Continuous working voltage shall be $\sqrt{P \times R}$ or maximum working voltage, whichever is less

(3) $\pm 2 \%$ standard, $\pm 1 \%$ and $\pm 5 \%$ available

TECHNICAL SPECIFICATIONS

PARAMETER	UNIT	01 CIRCUIT	03 CIRCUIT	05 CIRCUIT
Rated dissipation at 70 $^{\circ}\text{C}$ per element	W	0.08	0.16	0.08
Limiting element voltage ⁽¹⁾	V_{DC}	50		
Voltage coefficient	ppm/V	< 50		
Insulation voltage (1 min)	$V_{DC/AC}$ peak	200		
Category temperature range	$^{\circ}\text{C}$	-55 / +150		
Insulation resistance	Ω	$> 10^{10}$		
TC tracking (-55 $^{\circ}\text{C}$ to +125 $^{\circ}\text{C}$)	ppm/ $^{\circ}\text{C}$	50		

Note

(1) Rated voltage: $\sqrt{P \times R}$



GLOBAL PART NUMBER INFORMATION

New Global Part Numbering: SOMC16011K00GDC (preferred part numbering format)

S	O	M	C	1	6	0	1	1	K	0	0	G	D	C			
GLOBAL MODEL	PIN COUNT	SCHEMATIC	RESISTANCE VALUE	TOLERANCE CODE	PACKAGING			SPECIAL									
SOMC	14 16 20	01 = bussed 03 = isolated 00 = special	R = Ω K = k Ω M = M Ω 10R0 = 10 Ω 680K = 680 k Ω 1M00 = 1.0 M Ω 0000 = 0 Ω jumper	F = $\pm 1\%$ G = $\pm 2\%$ J = $\pm 5\%$ S = special Z = 0 Ω jumper	EJ = lead (Pb)-free, tube EA = lead (Pb)-free, tape and reel DC = tin / lead, tube RZ = tin / lead, tape and reel			Blank = standard (dash number) (up to 3 digits) from 1 to 999 as applicable									

Historical Part Number Example: SOMC1601102G (will continue to be accepted)

SOMC	16	01	102	G	D02
HISTORICAL MODEL	PIN COUNT	SCHEMATIC	RESISTANCE VALUE	TOLERANCE CODE	PACKAGING

New Global Part Numbering: SOMC2005500BGRZ (preferred part numbering format)

S	O	M	C	2	0	0	5	5	0	0	B	G	R	Z			
GLOBAL MODEL	PIN COUNT	SCHEMATIC	RESISTANCE VALUE	TOLERANCE CODE	PACKAGING			SPECIAL									
SOMC	14 16 20	05 = dual terminator	3 digit impedance code, followed by alpha modifier (see Impedance table)	F = $\pm 1\%$ G = $\pm 2\%$ J = $\pm 5\%$	EJ = lead (Pb)-free, tube EA = lead (Pb)-free, tape and reel DC = tin / lead, tube RZ = tin / lead, tape and reel			Blank = standard (dash number) up to 3 digits from 1 to 999 as applicable									

Historical Part Number Example: SOMC2005820131G (will continue to be accepted)


SOMC	20	05	820	131	G	R61
HISTORICAL MODEL	PIN COUNT	SCHEMATIC	RESISTANCE VALUE 1	RESISTANCE VALUE 2	TOLERANCE CODE	PACKAGING

Note

- For additional information on packaging, refer to the Surface Mount Network Packaging document (www.vishay.com/doc?31540)

CIRCUIT APPLICATIONS


01 Schematic



13, 15, or 19 resistors with one pin common
The SOMCxx01 circuit provides a choice of 13, 15, or 19 nominally equal resistors, each connected between a common lead (14, 16, or 20) and a discrete PC board pin. Commonly used in the following applications:

- MOS/ROM pull-up/pull-down
- Open collector pull-up
- "Wired OR" pull-up
- Power driven pull-up
- TTL input pull-down
- Digital pulse squaring
- TTL unused gate pull-up
- High speed parallels pull-up


03 Schematic



7, 8, or 10 isolated resistors
The SOMCxx03 circuit provides a choice of 7, 8, or 10 nominally equal resistors with each resistor isolated from all others and wired directly across. Commonly used in the following applications:


- "Wired OR" pull-up
- Power driven pull-up
- Powergate pull-up
- Line termination
- Long-line Impedance balancing
- LED current limiting
- ECL output pull-down
- TTL input pull-down

05 Schematic



TTL dual-line terminator; pulse squaring, 12, 14, or 18 pairs of resistors
(R_1 resistors are common to leads 14, 16, or 20)
(R_2 resistors are common to leads 7, 8, or 10)
The SOMCxx05 circuit contains 12, 14, or 18 pairs of resistors. Each pair is connected between ground and a common line. The junctions of these resistor pairs are connected to the input leads.
The 05 circuits are designed for TTL dual-line termination and pulse squaring.

DIMENSIONS



SOLDER PAD DIMENSIONS in millimeters

	a	b	c	l	p	w
WAVE	0.64	1.91	5.34	9.53	1.27	9.15
REFLOW	0.64	1.91	5.34	9.53	1.27	9.15

Notes

- The dimension shown are for a 16 pin part. For parts with different pin numbers use the same pitch and add or subtract pads as required
- Maximum solder reflow temperature +255 °C

DIMENSIONS in millimeters

PIN NO#	L	W	B	E	F	G	H	K	R	S	T
14	9.91	7.62	7.62	6.20	5.59	2.16	2.03	0.914	0.457	1.27	1.14
16	11.18	7.62	8.89	6.20	5.59	2.16	2.03	0.914	0.457	1.27	1.14
20	13.72	7.62	11.43	6.20	5.59	2.16	2.03	0.914	0.457	1.27	1.14
Tol.	± 0.254	± 0.381	± 0.254	± 0.381	± 0.127	± 0.127	± 0.127		± 0.076	± 0.254	

MARKING INFORMATION

1 % parts have 4 digits while 2 % and 5 % parts have 3 digits.

**IMPEDANCE CODES**

CODE	R ₁ (Ω)	R ₂ (Ω)	CODE	R ₁ (Ω)	R ₂ (Ω)
500B	82	130	141A	270	270
750B	120	200	181A	330	390
800C	130	210	191A	330	470
990A	160	260	221B	330	680
101C	180	240	281B	560	560
111C	180	270	381B	560	1.2K
121B	180	390	501C	620	2.7K
121C	220	270	102A	1.5K	3.3K
131A	220	330	202B	3K	6.2K

Note

- For additional impedance codes, refer to the Dual Terminator Impedance Code Table document (www.vishay.com/doc?31530)

PERFORMANCE

TEST	CONDITIONS OF TEST	TEST RESULTS (TYPICAL TEST LOTS)
Power conditioning	MIL-STD-202	± 0.5 %
Load life at 70 °C	MIL-STD-202	± 0.5 %
Short time overload	MIL-STD-202	± 0.25 %
Thermal shock	MIL-STD-202	± 0.5 %
Moisture resistance	MIL-STD-202	± 0.5 %
Resistance to soldering heat	MIL-STD-202	± 0.25 %
Low temperature operation	MIL-STD-202	± 0.25 %
Vibration	MIL-STD-202	± 0.25 %
Shock	MIL-STD-202	± 0.25 %
Terminal strength	MIL-STD-202	± 0.25 %

MECHANICAL SPECIFICATIONS

Marking	Model number, schematic number, value tolerance, pin 1 indicator, date code
Marking resistance to solvents	Permanency testing per MIL-STD-202, method 215
Maximum solder reflow temperature	+255 °C
Solderability	Per MIL-STD-202, method 208E
Terminals	Copper alloy. Solder dipped terminal
Body	Molded epoxy



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Vishay products are not designed for use in life-saving or life-sustaining applications or any application in which the failure of the Vishay product could result in personal injury or death unless specifically qualified in writing by Vishay. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.