




Case Outline for PowerPAK® 8 x 8 LR BWL (PP8X8LRWLK) (HVM)



DIM.	MILLIMETERS			INCHES		
	MIN.	NOM.	MAX.	MIN.	NOM.	MAX.
A	1.55	1.60	1.65	0.061	0.063	0.065
A1_LP	0.035	0.085	0.135	0.001	0.003	0.005
A1_HP	0.035	0.085	0.135	0.001	0.003	0.005
b	0.97	1.05	1.13	0.038	0.041	0.044
b1	1.07	1.15	1.23	0.042	0.045	0.048
c	0.254 ref.			0.010 ref.		
c1	1.26 ref.			0.050 ref.		
c2	0.63 ref.			0.025 ref.		
D	8.00	8.10	8.20	0.315	0.319	0.323
D1	7.80	7.90	8.00	0.307	0.311	0.315
D2	6.70	6.80	6.90	0.264	0.268	0.272
D5	0.90	1.00	1.10	0.035	0.039	0.043
e	2.00 BSC.			0.079 BSC.		
e1	6.00 BSC.			0.236 BSC.		
E	9.92	10.17	10.42	0.391	0.400	0.410
E1	6.12	6.22	6.32	0.241	0.245	0.249
E2	4.21	4.31	4.41	0.166	0.170	0.174
E3	6.18	-	6.43	0.243	-	0.253
E4	3.80	3.90	4.00	0.150	0.154	0.157
E5	4.70 ref.			0.185 ref.		
L_H	0.90	-	1.15	0.035	-	0.045
L_L	0.90	-	1.15	0.035	-	0.045
L1	1.80	-	2.10	0.071	-	0.083
L2	1.80	-	2.10	0.071	-	0.083
z1	0.45	0.55	0.65	0.018	0.022	0.026
z2	1.81	1.91	2.01	0.071	0.075	0.079
θ	0°	-	5°	0°	-	5°
eee	0.08			0.003		

ECN: C25-0394-Rev. C, 21-Apr-2025

DWG: 6110