


High Voltage Ceramic Capacitor Stacks, with Solder Tags, Class 2 Ceramic



QUICK REFERENCE DATA		
DESCRIPTION	VALUE	
Ceramic Class	2	
Ceramic Dielectric	R2005	
Type	GFMQ10..., GFWQ10..	GFMQ12..., GFWQ12..
Voltage (V_{DC})	8000	
Min. Capacitance (pF)	370	500
Max. Capacitance (pF)	370	500
Mounting	Solder tags	

MATERIAL

Capacitor elements made from class 2 ceramic dielectric with noble metal electrodes.

Connection terminals between the discs: brass, silver plated

OPTIONAL TERMINALS

We offer a variety of intermediate solder tags to meet customers requirements. Please contact us.

FEATURES

- Small size
- Multiple design up to 12 stages
- Voltage rating of the individual discs 8 kV_{DC}
- Other versions on request

APPLICATIONS

Ceramic capacitor stacks have been developed for use in low power voltage multipliers used in high voltage DC generators. The major applications are x-ray equipment for medical diagnostics or electrostatic paint spraying equipment.

CAPACITANCE RANGE

370 pF to 500 pF

CAPACITANCE TOLERANCE

± 20 %

CERAMIC DIELECTRIC

R2005 (X7R)

RATED VOLTAGE

8.0 kV_{DC} per single disc

DIELECTRIC STRENGTH TEST

13 kV_{DC} per single disc, in dielectric fluid

DISSIPATION FACTOR

Max. 2.5 % (1 kHz)

INSULATION RESISTANCE

Min. 10 GΩ (at 25 °C)

OPERATING TEMPERATURE RANGE





-25 °C to +85 °C

SAP PART NUMBER AND ELECTRICAL DATA

PART NUMBER	CERAMIC	CAPACITANCE VALUES ⁽¹⁾ (pF)	RATED VOLTAGE ⁽¹⁾⁽²⁾ (kV _{DC})	TEST VOLTAGE ⁽¹⁾⁽³⁾ (kV _{DC})	NO. OF DISC IN SERIES	L _{MAX.} mm (INCH)	D mm (INCH)
TYPE GFMQ10..							
RHS370P38BPZHA6000	R2005 (X7R)	370 (± 20 %)	8.0	13	10	61.5 (2.421)	10.5 ± 0.3 (0.413 ± 0.012)
RHS370P38BPZHB6001					12	73.5 (2.893)	
TYPE GFWQ10..							
RHS370P38BPZHC6002	R2005 (X7R)	370 (± 20 %)	8.0	13	10	61.5 (2.421)	10.5 ± 0.3 (0.413 ± 0.012)
RHS370P38BPZHD6003					12	73.5 (2.893)	
TYPE GFMQ12..							
RHS500P38BPZHE6004	R2005 (X7R)	500 (± 20 %)	8.0	13	8	49.5 (1.949)	12.0 ± 0.2 (0.472 ± 0.008)
RHS500P38BPZHF6005					10	61.5 (2.421)	
RHS500P38BPZHG6006					12	73.5 (2.893)	
TYPE GFWQ12..							
RHS500P38BPZHH6007	R2005 (X7R)	500 (± 20 %)	8.0	13	8	49.5 (1.949)	12.0 ± 0.2 (0.472 ± 0.008)
RHS500P38BPZHJ6008					10	61.5 (2.421)	
RHS500P38BPZHK6009					12	73.5 (2.893)	

Notes

- ⁽¹⁾ Per single disc
⁽²⁾ In an insulating environment
⁽³⁾ Min. 3 s in dielectric fluid

DIMENSIONS DATA
TYPE GFMQ

TYPE GFWQ

RELATED DOCUMENTS

General Information

www.vishay.com/doc?22090



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Vishay products are not designed for use in life-saving or life-sustaining applications or any application in which the failure of the Vishay product could result in personal injury or death unless specifically qualified in writing by Vishay. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.