



Ref. Certif. No.

US-45518-UL

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

CB TEST CERTIFICATE

Product

Fixed Capacitors for Electromagnetic Interference Suppression and Connection to The Supply Mains, Disc Type

Name and address of the applicant

Vishay Electronic GmbH
Dr. Felix-Zandman-Platz 1 Selb 95100
Germany

Name and address of the manufacturer

Vishay Electronic GmbH
Dr. Felix-Zandman-Platz 1 Selb 95100
Germany

Name and address of the factory

VISHAY COMPONENTS (HUIZHOU) CO LTD
46, Renmin 4 Road, Danshui Town, Huiyang Zone HUIZHOU, Guangdong,
516211
China


Note: When more than one factory, please report on page 2

☐ Additional Information on page 2

Ratings and principal characteristics

X1-760Vac, Y1- 500Vac, 470 pF to 4700 pF, 40/125/21/B Capacitance tolerance K($\pm 10\%$) or M($\pm 20\%$)

Trademark / Brand (if any)



Customer's Testing Facility (CTF) Stage used

Model / Type Ref.

VKP series

Additional information (if necessary may also be reported on page 2)

National Differences: EU Group Differences
☐ Additional Information on page 2

A sample of the product was tested and found to be in conformity with

IEC 60384-14:2023

As shown in the Test Report Ref. No. which forms part of this Certificate

E183844-4791532674-2 Original issued on 2025-08-08

This CB Test Certificate is issued by the National Certification Body



- ☒ UL Solutions (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
- ☐ UL Solutions (Denko), Borupvang 5A DK-2750 Ballerup, DENMARK
- ☐ UL Solutions (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- ☐ UL Solutions (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/ncbnames

Date: 2025-08-12

Signature:

Mauricio Avila