

High Current Thermal Fuse



The HCTF EL series is especially designed for high current applications with an operating temperature up to 160 °C. In case of excess heat in the range of the functioning temperature of $(235 \pm 15) ^\circ\text{C}$ the thermo fuse opens automatically and disconnects the circuit. Typical applications are automotive power electronics that are connected to steady battery power (B+ or terminal number 30).

FEATURES

- Functioning temperature: $\vartheta_F = (235 \pm 15) ^\circ\text{C}$
- Holding temperature: $\vartheta_H = 160 ^\circ\text{C}$
- Current: $\leq 80 \text{ A}$
- Suitable for resistive welding systems
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912


RoHS
COMPLIANT

APPLICATIONS


- Automotive
 - Fan control units
 - ABS
 - Diesel glow plug relays
 - Diesel pre-heaters
 - Electric coolant pumps

TECHNICAL SPECIFICATIONS	
DESCRIPTION	HCTF 235 EL
Functioning temperature ϑ_F	$(235 \pm 15) ^\circ\text{C}$
Holding temperature ϑ_H (1000 h)	160 °C
Voltage U_{DC}	24 V
Current $I_{DC}^{(1)}$	$\leq 80 \text{ A}$
Cold resistance R_{cold}	$\leq 0.1 \text{ m}\Omega$
Residual resistance R_s	$> 1 \text{ M}\Omega$

Note

⁽¹⁾ Current rating depends on external thermal resistivity

DIMENSIONS



DIMENSIONS - Mass and relevant physical dimensions					
TYPE	W_1 (mm)	W_2 (mm)	$D_1^{(1)}$ (mm)	D_2 (mm)	MASS (g)
HCTF EL	26 ± 0.5	6.5 ± 0.5	7.7 ± 0.3	1.8 ± 0.2	1.45 ± 0.3

Note

⁽¹⁾ Between sleek surfaces

PART NUMBER AND PRODUCT DESCRIPTION ⁽¹⁾

PART NUMBER: HCTF235L280000BR00

H	C	T	F	2	3	5	L	2	8	0	0	0	0	B	R	0	0
TYPE / FUNCTIONING TEMPERATURE				TOLERANCE		SPECIAL				CURRENT				PACKAGING		SPECIAL	
HCTF235				L = ± 15 °C		1 digit 2 = weldable extended length				Current in mA. 80000 = 80 A				BR		Up to 2 digits 00 = standard	

PRODUCT DESCRIPTION: HCTF 235 15 °C EL BR 80A0

HCTF	235	15 °C	EL	BR	80A0
TYPE	FUNCTIONING TEMPERATURE	TOLERANCE	SPECIAL	PACKAGING	CURRENT
HCTF	235	± 15 °C	EL = extended length	BR	80A0 = 80 A

Note

⁽¹⁾ Products can be ordered using either the PART NUMBER or the PRODUCT DESCRIPTION

PACKAGING

TYPE	CODE	QUANTITY	CARRIER TAPE	WIDTH	PITCH	REEL DIAMETER
HCTF EL	BR	750	Blister tape acc. IEC 60286-3 Type III	44 mm	12 mm	360 mm/14.2"

ASSEMBLY

The high current thermal fuse HCTF 235 EL is suitable for processing on e.g. automatic electric resistance welding or crimping assembly systems. Any deformation and overheating of the component body to levels above the holding temperature has to be avoided during the assembly.

MATERIALS

Vishay acknowledges the following systems for the regulation of hazardous substances:

- IEC 62474, Material Declaration for Products of and for the Electrotechnical Industry, with the list of declarable substances given therein ⁽¹⁾
- The Global Automotive Declarable Substance List (GADSL) ⁽²⁾
- The REACH regulation (1907/2006/EC) and the related list of substances with very high concern (SVHC) ⁽³⁾ for its supply chain

The products do not contain any of the banned substances as per IEC 62474, GADSL, or the SVHC list, see www.vishay.com/how/leadfree.

Hence the products fully comply with the following directives:

- 2000/53/EC End-of-Life Vehicle Directive (ELV) and Annex II (ELV II)
- 2011/65/EU Restriction of the Use of Hazardous Substances Directive (RoHS) with amendment 2015/863/EU
- 2012/19/EU Waste Electrical and Electronic Equipment Directive (WEEE)

Vishay pursues the elimination of conflict minerals from its supply chain, see the Conflict Minerals Policy at www.vishay.com/doc?49037.

Notes

- ⁽¹⁾ The IEC 62474 list of declarable substances is maintained in a dedicated database, which is available at <http://std.iec.ch/iec62474>
- ⁽²⁾ The Global Automotive Declarable Substance List (GADSL) is maintained by the American Chemistry Council and available at www.gadsl.org
- ⁽³⁾ The SVHC list is maintained by the European Chemical Agency (ECHA) and available at <http://echa.europa.eu/candidate-list-table>



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Vishay products are not designed for use in life-saving or life-sustaining applications or any application in which the failure of the Vishay product could result in personal injury or death unless specifically qualified in writing by Vishay. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.