

Leaded Wirewound Resistors, Surface Mount, Silicone or Cement Coated, High Power



FEATURES

- Low cost, high power (up to 3.75 W)
- All welded construction
- Ideal for pulsing application
- Ceramic core
- Available on tape and reel
- Material categorization:
for definitions of compliance please see
www.vishay.com/doc?99912



Note

* This datasheet provides information about parts that are RoHS-compliant and / or parts that are non RoHS-compliant. For example, parts with lead (Pb) terminations are not RoHS-compliant. Please see the information / tables in this datasheet for details

STANDARD ELECTRICAL SPECIFICATIONS

GLOBAL MODEL	SIZE	POWER RATING $P_{25^{\circ}\text{C}}$ W	RESISTANCE RANGE ⁽¹⁾ Ω TCR (-10 to -80) ppm/K ⁽²⁾ (CLASS 1)	RESISTANCE RANGE ⁽¹⁾ Ω TCR (100 to 180) ppm/K (CLASS 3)	RESISTANCE RANGE Ω TCR ± 50 ppm/ $^{\circ}\text{C}$	RESISTANCE RANGE Ω TCR ± 30 ppm/ $^{\circ}\text{C}$	TOLERANCE $\pm$ %	WEIGHT (typical) g	ENCAPS.
WSZ7532	7532	3.75	n/a	n/a	n/a	10 to 15K	1, 3	0.7	Silicone
			n/a	n/a	1 to 9.99	10 to 15K	5, 10		

Notes

(1) Lower TCR or other power range on request. Resistance value to be selected for ± 10 % tolerance from E12 and for ± 5 % from E24

(2) $\leq 1 \Omega \leq 400$ ppm/K

(3) Power rating depends on the maximum temperature at the solder point, solder pad dimensions, the component placement density and the substrate material

GLOBAL PART NUMBER INFORMATION

Global Part Numbering Example: WSZ75321K000JTA

W	S	Z	7	5	3	2	1	K	0	0	0	J	T	A			
---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	--	--	--

GLOBAL MODEL

WSZ7532

VALUE

R = decimal
K = thousand
54R15 = 54.15 Ω
1K325 = 1325 Ω

TOLERANCE CODE

F = ± 1.0 %
G = ± 2.0 %
H = ± 3.0 %
J = ± 5.0 %
K = ± 10 %


PACKAGING

EA = lead (Pb)-free, tape / reel
TA = tin / lead, tape / reel

SPECIAL

(dash number)
(up to 3 digits)
From **1 to 999**
as applicable

DIMENSIONS



MODEL	DIMENSIONS in millimeters (inches)					
	A	B	C	D	E	Z
WSZ7532	14.27 ± 1.57 (0.562 ± 0.062)	19.86 ± 0.548 - 0.381 (0.782 ± 0.021 - 0.015)	4.78 ± 0.8 (0.188 ± 0.031)	0.813 ± 0.051 (0.032 ± 0.002)	7.33 ± 1.6 (0.289 ± 0.062)	6.5 ± 1.12 (0.256 ± 0.044)

MODEL	SOLDER PAD DIMENSIONS in millimeters (inches)		
	a	b	l
WSZ7532	4.0 (0.157)	9.50 (0.374)	15.05 (0.593)


TECHNICAL SPECIFICATIONS

PARAMETER	UNIT	WSZ7532
Temperature Coefficient	ppm/°C	See Standard Electrical Specifications table
Operating Temperature Range	°C	-65 to +350
Maximum Working Voltage	V	$(P \times R)^{1/2}$
Terminal Strength	lb	10 minimum

PERFORMANCE


TEST	CONDITIONS OF TEST	TEST LIMITS
Temperature Cycling	-55 °C to +125 °C, 5 cycles, 15 min at each extreme	± (2 % + 0.05 Ω) ΔR
High Temperature Exposure	1000 h at +250 °C	± (2 % + 0.05 Ω) ΔR
Short Time Overload	5 x rated power for 5 s	± (2 % + 0.05 Ω) ΔR
Shock, Specified Pulse	100 g's for 6 ms, 10 shocks	± (2 % + 0.05 Ω) ΔR
Vibration, High Frequency	Frequency varied 10 Hz to 2000 Hz, 20 g peak, 2 directions 6 h each	± (2 % + 0.05 Ω) ΔR
Load Life	2000 h at rated power, +25 °C, 1.5 h "ON", 0.5 h "OFF"	± (3 % + 0.05 Ω) ΔR
Resistance to Soldering Heat	+260 °C solder, 10 s to 12 s dwell, 25 mm/s emergence	± (0.5 % + 0.05 Ω) ΔR

TEMPERATURE RISE



Measurement based on recommended solder pads

DERATING



PACKAGING

MODEL	REEL			
	TAPE WIDTH	DIAMETER	PIECES/REEL	CODE
WSZ7532 ⁽¹⁾	32 mm / embossed plastic	330 mm / 13"	350	EA/TA

Note

⁽¹⁾ Embossed carrier tape per EIA-481



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Vishay products are not designed for use in life-saving or life-sustaining applications or any application in which the failure of the Vishay product could result in personal injury or death unless specifically qualified in writing by Vishay. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.