


Thick Film Resistor Networks, Dual-In-Line, Molded DIP



FEATURES

- TTL/ECL translator and SCSI-BUS signal terminator schematics available
- 0.190" (4.83 mm) maximum seated height
- Rugged, molded case construction
- Low temperature coefficient (-55 °C to +125 °C),
MDP 1645: ± 100 ppm/°C,
MDP 1646: ± 250 ppm/°C
- Compatible with automatic insertion equipment
- Thick film resistive elements
- Reduces PC board space and reduces total assembly costs
- Available in tube pack
- Material categorization: For definitions of compliance please see www.vishay.com/doc?99912


RoHS*
Available

Note


* This datasheet provides information about parts that are RoHS-compliant and/or parts that are non-RoHS-compliant. For example, parts with lead (Pb) terminations are not RoHS-compliant. Please see the information/tables in this datasheet for details.

STANDARD ELECTRICAL SPECIFICATIONS

GLOBAL MODEL/ PIN NO.	POWER RATING ELEMENT $P_{70^{\circ}\text{C}}$ W	POWER RATING PACKAGE $P_{70^{\circ}\text{C}}$ W	TOLERANCE $\pm \%$	RESISTANCE VALUES Ω	TEMPERATURE COEFFICIENT (-55 °C to +125 °C) $\pm$ ppm/°C (Typ.)	TCR TRACKING $\pm$ ppm/°C	WEIGHT g
MDP1645	0.125	2.0	2	180, 270, 820	100	150	1.5
MDP1646	0.125	2.0	5	330, 150	250	150	1.5

CIRCUIT APPLICATIONS


MDP1645 Schematic



TTL to ECL translator

The MDP1645 network consists of 18 resistors of 3 different values, internally divided into six (6) identical three (3) resistor sections for TTL to ECL translation.

MDP1646 Schematic



SCSI-BUS signal terminator

The MDP1646 network consists of 21 resistors of 2 different values, internally divided into seven (7) identical three (3) resistor sections for SCSI-BUS terminator applications.

GLOBAL PART NUMBER INFORMATION

New Global Part Numbering: MDP1646D04 (preferred part number information)



M	D	P	1	6	4	6	D	0	4					
GLOBAL MODEL			PIN COUNT			SCHEMATIC			PACKAGING			SPECIAL		
MDP			16			45 = TTL/ECL translator 46 = Signal terminator			E04 = Lead (Pb)-free, tube D04 = Tin/lead, tube			Blank = Standard (Dash number) (Up to 3 digits) From 1 to 999 as applicable		

Historical Part Number: MDP1646 (will continue to be accepted)

MDP	16	46	D04
HISTORICAL MODEL	PIN COUNT	SCHEMATIC	PACKAGING

Note

- For additional information on packaging, refer to the Through-Hole Network Packaging document (www.vishay.com/doc?31542).

**DIMENSIONS** in inches (millimeters)**TECHNICAL SPECIFICATIONS**

PARAMETER	UNIT	MDP SERIES
Maximum Operating Voltage	V _{DC}	100
Voltage Coefficient of Resistance (Typical)	V _{eff}	< 50 ppm/°C
Operating Temperature Range	°C	-55 to +125
Storage Temperature Range	°C	-55 to +150

MECHANICAL SPECIFICATIONS

Marking Resistance to Solvents	Permanency testing per MIL-STD-202, method 215
Solderability	Per MIL-STD-202, method 208E
Terminals	Copper alloy, solder plated
Body	Molded epoxy
Weight	1.5 g

PERFORMANCE

TEST	CONDITIONS	MAX. ΔR (TYPICAL TEST LOTS)
Thermal Shock	5 cycles between -65 °C and +125 °C	± 0.50 % ΔR
Short Time Overload	2.5 x rated working voltage 5 s	± 0.25 % ΔR
Low Temperature Operation	45 min at full rated working voltage at -65 °C	± 0.25 % ΔR
Moisture Resistance	240 h with humidity ranging from 80 % RH to 98 % RH	± 0.50 % ΔR
Resistance to Soldering Heat	Leads immersed in +260 °C solder to within 1/16" of body for 10 s	± 0.25 % ΔR
Shock	Total of 18 shocks at 100 g's	± 0.25 % ΔR
Vibration	12 h at maximum of 20 g's between 10 Hz and 2000 Hz	± 0.25 % ΔR
Load Life	1000 h at +70 °C, rated power applied 1.5 h "ON", 0.5 h "OFF" for full 1000 h period. Derated according to the curve.	± 0.50 % ΔR
Terminal Strength	4 1/2 pound pull for 30 s	± 0.25 % ΔR
Insulation Resistance	10 000 MΩ (minimum)	-
Dielectric Withstanding Voltage	No evidence of arcing or damage (200 V _{RMS} for 1 min)	-



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Vishay products are not designed for use in life-saving or life-sustaining applications or any application in which the failure of the Vishay product could result in personal injury or death unless specifically qualified in writing by Vishay. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.