



High Current, SMD Common Mode Choke



FEATURES

- Wirewound ferrite common mode choke
- 12.0 mm x 11.0 mm x 6.0 mm SMD package
- Material categorization:
for definitions of compliance please see
www.vishay.com/doc?99912



RoHS
COMPLIANT
HALOGEN
FREE
GREEN
(5-2008)

APPLICATIONS

- DC/DC power supplies
- LCD displays
- Noise suppression and filtering
- Lighting drivers
- Battery powered devices

LINKS TO ADDITIONAL RESOURCES



Product Page

ELECTRICAL SPECIFICATIONS

Resistance to solder heat: 245 °C peak for < 30 s (3 times max. through reflow)

STANDARD ELECTRICAL SPECIFICATIONS

PART NUMBER	COMMON MODE IMPEDANCE, AT 10 MHz, TYP. (Ω)	COMMON MODE IMPEDANCE, AT 100 MHz, TYP. (Ω)	DCR MAX. 25 °C (mΩ)	HEAT RATING CURRENT DC TYP. (A) ⁽¹⁾
ICM5050ER501R	160	500	4	11
ICM5050ER701N	210	700	5	9
ICM5050ER102N	340	1000	8	7
ICM5050ER172N	850	1700	12	5.5

Notes

- All test data is referenced to 25 °C ambient
 - DCR specification is for a single coil
 - Rated operating voltage = 80 V_{DC}
 - Insulating resistance 10 MΩ min.
 - Operating temperature range -40 °C to +125 °C
 - Storage condition: -40 °C to +125 °C (on board); less than 40°C and < 60 % RH (in component packaging)
- ⁽¹⁾ DC current (A) that will cause an approximate ΔT of 40 °C

DIMENSIONS in inches [millimeters]

A	B	C	D	E	F	G	L	H	G1	G2
0.472 ± 0.020 [12.0 ± 0.5]	0.433 ± 0.012 [11.0 ± 0.3]	0.236 max. [6.0 max.]	0.264 typ. [6.7 typ.]	0.106 ± 0.020 [2.7 ± 0.5]	0.102 ± 0.020 [2.6 ± 0.5]	0.102 ± 0.020 [2.6 ± 0.5]	0.551 ref. [14.0 ref.]	0.311 ref. [7.9 ref.]	0.291 ref. [7.4 ref.]	0.098 ref. [2.5 ref.]



GLOBAL PART NUMBER

I C M

PRODUCT
FAMILY

5 0 5 0

SIZE

E R

PACKAGE CODE

ER = tape and reel

5 0 1

IMPEDANCE
VALUE

501 = 500 Ω

R


TOLERANCE

N = 25 %


R = 50 %

SCHEMATICS


Common Mode Impedance




Differential Mode Impedance



DC Resistance







Insulation Resistance





PERFORMANCE GRAPHS





Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Vishay products are not designed for use in life-saving or life-sustaining applications or any application in which the failure of the Vishay product could result in personal injury or death unless specifically qualified in writing by Vishay. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.