

Space Grade Surface-Mount Common Mode Choke



ABSOLUTE MAXIMUM RATINGS

PARAMETER	CONDITIONS	LIMITS	UNITS
Dielectric withstand voltage (DWW) ⁽¹⁾	Windings to windings, windings to core	1000	V _{RMS}
Insulation resistance (IR) ⁽²⁾	Windings to windings and core, 10 GΩ min.	500	V _{DC}
Operating temperature	Continuous	-55 to +130	°C
Storage temperature	Continuous	-65 to +155	°C
Maximum weight		5.5	g

Notes

- ⁽¹⁾ Test conditions adjusted per MIL-STD-981 and MIL-PRF-27 4.7.9.1 during group A and B testing, applies to all external materials
- ⁽²⁾ Test conditions adjusted per MIL-STD-981 and MIL-PRF-27 4.7.11 during group A and B testing, applies to all external materials

FEATURES

- Nanocrystalline based design
- Self-shielded
- Molded construction for ruggedized applications
- MIL-PRF-27 grade 5, product level T, temperature class S
- MIL-STD-981 family 04 power inductor, class S compliant ⁽¹⁾⁽²⁾
- ASTM-E595 outgassing compliant ⁽³⁾
- Tin-lead terminations
- Broadband frequency attenuation
- Customization available (e.g., turns count, wire gauge, temperature class, screening, etc.)

Notes

- ⁽¹⁾ Screening codes S and B only
- ⁽²⁾ Clarifications to MIL-STD-981 (1):
 - a. MIL-STD-981 figures 3b, c, and d do not apply to this assembly's build construction
 - b. Corona discharge is not applicable
- ⁽³⁾ Applies to all external materials

APPLICATIONS

- GaN and SiC switching devices
- Low profile, high current power supplies
- DC/DC converters in distributed power systems
- Power converter for solar panels
- Noise suppression


STANDARD ELECTRICAL SPECIFICATIONS

PART NUMBER	L ₀ INDUCTANCE PER WINDING ± 40 % AT 10 kHz, 0.10 V, 0 A (μH)	COMMON MODE IMPEDANCE, AT 10 MHz, TYP. (Ω)	DC RESISTANCE MAX. PER WINDING (Ω)	HEAT RATING CURRENT DC TYP. (A) ⁽¹⁾	PEAK IMPEDANCE FREQUENCY (MHz)	LEAKAGE MAX. (μH)
SGCM05339T321_	320	540	0.0029	14.43	31.74	0.35
SGCM05339T581_	580	930	0.0049	10.69	19.87	0.45
SGCM05339T901_	900	1440	0.0077	8.71	14.06	0.65
SGCM05339T132_	1300	2080	0.0118	7.14	10.78	0.95
SGCM05339T182_	1800	2960	0.0172	5.89	8.82	1.35
SGCM05339T232_	2300	3310	0.0197	5.53	6.76	1.75
SGCM05339T292_	2900	3740	0.0278	4.71	5.93	2.75
SGCM05339T362_	3600	4000	0.0309	4.20	5.02	3.25
SGCM05339T442_	4400	4040	0.0430	3.86	4.14	4.00
SGCM05339T522_	5200	3950	0.0589	3.32	3.73	4.25
SGCM05339T612_	6100	3980	0.0638	3.19	3.49	4.50
SGCM05339T712_	7100	3920	0.0873	2.73	2.89	5.00
SGCM05339T812_	8100	3880	0.0935	2.63	2.72	5.50
SGCM05339T922_	9200	3820	0.1240	2.02	2.25	6.50
SGCM05339T103_	10 400	3600	0.1318	2.02	2.06	7.75

Notes

- All test data is referenced to 25 °C ambient
 - The part temperature (ambient + temp. rise) should not exceed 130 °C under worst case operating conditions. Circuit design, component placement, PWB trace size and thickness, airflow and other cooling provisions all affect the part temperature. Part temperature should be verified in the end application
 - Specify desired screening code in " " placeholder at end of part number: P = production screened, L = low earth orbit (LEO) screened, B = MIL-STD-981 class B screened, S = MIL-STD-981 class S screened
- ⁽¹⁾ DC current (A) through the windings in series that will cause an approximate ΔT of 30 °C

DIMENSIONS in inches [millimeters]

Schematic 1

DESCRIPTION
SGCM05339

MODEL

T = TAPE

PACKAGE CODE

320 μ H

INDUCTANCE VALUE

S ⁽¹⁾

SCREENING CODE

Note
⁽¹⁾ Reference "Screening Breakdown" table

GLOBAL PART NUMBER

S	G	C	M	0	5	3	3	9	T	3	2	1	S
PRODUCT FAMILY				SIZE					PACKAGE CODE	INDUCTANCE VALUE			SCREENING
										321 = 320 μ H			

Note







- For additional packaging details see ["Packaging Methods"](#)



SCREENING BREAKDOWN						
	P = PRODUCTION SCREENED	L = LOW EARTH ORBIT (LEO) SCREENED	E3 = EEE-INST-002 LEVEL 3 SCREENED	E2 = EEE-INST-002 LEVEL 2 SCREENED	B = MIL-STD-981 TABLE VI CLASS B SCREENED	S = MIL-STD-981 TABLE VI AND XII CLASS S SCREENED
PRODUCTION SCREENING (sample size = 100 %)						
Electrical characteristics (continuity, inductance (L _s), turns ratio (TR), phase, leakage inductance, DWV, insulation resistance, DCR)	✓	✓	✓	✓	✓	✓
Mechanical inspection	✓	✓	✓	✓	✓	✓
Visual inspection	✓	✓	✓	✓	✓	✓
QUALITY CONFORMANCE SCREENING (group A) (sample size = 100 %)						
5 cycle thermal shock (-55 °C to +130 °C)	n/a	n/a	✓	n/a	n/a	n/a
10 cycle thermal shock (-55 °C to +130 °C)	n/a	✓	n/a	✓	n/a	n/a
96 hour burn-in at 130 °C (unpowered)	n/a	✓	n/a	✓	✓	✓
25 cycle thermal shock (-55 °C to +130 °C)	n/a	n/a	n/a	n/a	✓	✓
Dielectric withstanding voltage (DWV)	n/a	✓	✓	✓	✓	✓
Dielectric withstanding voltage (DWV) at altitude	n/a	n/a	✓	✓	n/a	n/a
Insulation resistance (IR)	n/a	✓	✓	✓	✓	✓
Electrical characteristics (continuity, L _s , TR, phase, leakage inductance, DCR)	n/a	✓	✓	✓	✓	✓
Radiographic inspection	n/a	n/a	n/a	n/a	n/a	✓
Mechanical inspection (sampled per table V; MIL-STD-981)	n/a	✓	n/a	n/a	✓	✓
Visual inspection (100 %)	n/a	✓	✓	✓	✓	✓
QUALIFICATION INSPECTION (group B) (lot sampling)						
MIL-STD-981 table XII	n/a	n/a	n/a	n/a	n/a	✓
EEE-INST-002 Table 3	n/a	n/a	n/a	Optional	n/a	n/a












PERFORMANCE GRAPHS: IMPEDANCE VS. FREQUENCY CHARACTERISTICS (common mode)





PERFORMANCE GRAPHS: IMPEDANCE VS. FREQUENCY CHARACTERISTICS (common mode)



PERFORMANCE GRAPHS: IMPEDANCE VS. FREQUENCY CHARACTERISTICS (common mode)




Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Vishay products are not designed for use in life-saving or life-sustaining applications or any application in which the failure of the Vishay product could result in personal injury or death unless specifically qualified in writing by Vishay. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.