


Massive Electro-Pyrotechnic Initiator AEC-Q200 Qualified Resistor Chip



DESIGN SUPPORT TOOLS

[click logo to get started](#)

3D
Models
Available

MEPIA is the AEC-Q200 qualified declination of Vishay MEPIC product.

The principle of MEPIA is to convert electrical energy into heat in a precise electro-thermal profile. Automotive applications cover airbags and security belts activation. Additional information about general purpose MEPIC product can be found here:

www.vishay.com/doc?53058

FEATURES

- AEC-Q200 qualified
- Surface mount design for standard assembly process
- SMD version only, with tin terminations
- Case size 0805
- Firing energy down to 0.5 mJ ⁽¹⁾
- Firing time down to 250 µs
- Ohmic value: 2 Ω
- Joule effect ignition
- Easy set up by design of firing levels
- Very predictable, reproducible and reliable behavior
- Compatibility with pyrotechnic element has to be tested in real environment
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912




RoHS
COMPLIANT

Note

- ⁽¹⁾ Ignitor performances are dependent on both pyrotechnic primer chemistry and active areas geometry

DIMENSIONS AND TOLERANCES in millimeters (inches)



MODEL	SIZE / CASE DESIGNATION	WIDTH W	LENGTH L	THICKNESS T	BACK SIDE PADS P	ACTIVE AREA WIDTH TOLERANCE A
MEPIA (SMD)	0805	2.00 ± 0.15 (0.080 ± 0.006)	1.25 ± 0.10 (0.050 ± 0.004)	0.6 ± 0.1 (0.024 ± 0.004)	0.45 ± 0.2 (0.018 ± 0.006)	± 0.01 (± 0.0004)

Notes

- For the assembly on board, we recommend the lead (Pb)-free thermal profile as per J-STD-020C
- Do not use iron soldering method to mount a MEPIA because it may damage the component (deformation that may cause active area cracks)

STANDARD ELECTRICAL SPECIFICATIONS

MODEL	SIZE / CASE DESIGNATION	RESISTANCE RANGE Ω	RESISTANCE TOLERANCE %
MEPIA (SMD)	0805	2	7.5 to 30

MECHANICAL SPECIFICATIONS

Mechanical protection	None
Resistive element	NiCr foil
Substrate	Epoxy based FRx
Terminations	Tin

PERFORMANCES				
TESTS	SPEC.	CONDITIONS	SPEC. REQUIREMENTS	TYPICAL PERFORMANCES
High temperature exposure	MIL-STD-202 Method 108	$T = 125^{\circ}\text{C} / 1000 \text{ h}$	$\pm 2 \% \pm 0.05 \Omega$	$\pm 1.5 \%$
Temperature cycling	JESD22 Method JA-104	$-55^{\circ}\text{C} / 125^{\circ}\text{C}$ 1000 cycles	$\pm 5 \% \pm 0.05 \Omega$	$\pm 1.5 \%$
Biased humidity	MIL-STD-202 Method 103	$85^{\circ}\text{C} / 85 \% \text{ RH}$ 1000 h	$\pm 2 \% \pm 0.05 \Omega$	$\pm 1.2 \%$
Operational life	MIL-STD-202 Method 108	$T = 125^{\circ}\text{C} / 1000 \text{ h}$ $P = 51 \text{ mW}$ (P based on no fire conditions)	$\pm 2 \% \pm 0.05 \Omega$	$\pm 1.6 \%$
Mechanical shock	MIL-STD-202 Method 213	100 G	$\pm 2 \% \pm 0.05 \Omega$	$\pm 0.2 \%$
Vibration	MIL-STD-202 Method 204	2000 Hz / 5G 10 cycles	$\pm 2 \% \pm 0.05 \Omega$	$\pm 0.2 \%$
Solderability	MIL-STD-202 Method 210 Cond. D	$T = 245^{\circ}\text{C} / 3 \text{ s}$	No degradation of termination side	Visual inspection: conform to spec.
ESD	AEC-Q200-002	Air discharge $U = 25 \text{ kV} / 1 \text{ time}$	$\pm 5 \% \pm 0.05 \Omega$	$\pm 1.5 \%$
Reflow	According to IPC-610 / vers. E § 8.3.2.6 / Fig. 8.35	Sn96.6Ag3Cu0.5 soldering	25 % of the height of the termination	Visual inspection: conform to spec.
Electrical characterization	User spec.	$-55^{\circ}\text{C} / 125^{\circ}\text{C}$ alumina board	$\pm 200 \text{ ppm}/^{\circ}\text{C}$	$\pm 160 \text{ ppm}/^{\circ}\text{C}$
Electrical characterization	User spec.	$-55^{\circ}\text{C} / 125^{\circ}\text{C}$ FR4 board	$\pm 200 \text{ ppm}/^{\circ}\text{C}$	$\pm 170 \text{ ppm}/^{\circ}\text{C}$
Board flex	AEC-Q200-005	60 s / 2 mm	$\pm 2 \% \pm 0.05 \Omega$	$\pm 0.2 \%$
Shear test	AEC-Q200-006	0.5 N / 60 s	$\pm 2 \% \pm 0.05 \Omega$	$\pm 0.8 \%$

RANGE OF IGNITION PERFORMANCES					
MODEL	"NO FIRE" CURRENT A	"NO FIRE" DURATION s	"ALL FIRE" CURRENT A	IGNITION TIME ms	"ALL FIRE" ENERGY μJ
MEPIA (SMD)	0.5 to 1.2	2 to 10	Down to 1	Down to 0.25	Down to 500

TECHNOLOGY

The MEPIA active area (heating zone) will be impregnated by the user with a primary pyrotechnic material (usually wet primer followed by drying) in such way to ensure an intimate contact for an optimum heat transfer of thermal energy. Note that the active area of MEPIA shall not be put in direct contact with explosive powder as grain size will not ensure intimate contact and will induce non reproducible and non reliable performances.

The two main characteristics of a MEPIA resistor are their "All Fire" (AF) and "No Fire" (NF) performances:

- "All Fire" (AF) represents the command pulse (generally with capacitance discharge) where the major amount of the dissipated energy will be transferred to the primer to generate the ignition
- "No Fire" (NF) represents the immunity of the resistor with primer to the environmental electro-magnetic pollution and electric continuity test, where the major amount of the dissipated energy will be transferred to the substrate to ensure no ignition

ASSEMBLY PRECAUTIONS

In order to obtain reproducible ignition performances it is important that the assembly process fulfills the following criteria:

- Take specific precautions, such as no air bubble during preparation and application of primer, in order to ensure the intimate contact of pyrotechnic primer and MEPIA active area (potential misfire)
- Take specific handling precaution in order not to damage MEPIA active area (ex: pickup head design for pick and place or specific fixing tools in the entire assembly process)
- All along the assembly process, take specific care to extreme thermo-mechanic stress that could be applied to the MEPIA (such as stress induced during over molding) because the active area of MEPIA is subjected to crack (and generate unstable resistance value)
- The MEPIA reliability is only guaranteed for one single reflow profile
- In case of necessity to dismantle a MEPIA, another MEPIA must be used (no rework is allowed)
- Pay specific attention to the cleaning process after reflow soldering in order not to damage the active area and to keep it clean from various pollution

ORDERING PROCEDURE

Global Part Numbering: MEPIA0805-2R0ILT09

M	E	P	I	A	0	8	0	5	-	2	R	0	I	L	T	0	9
MODEL		SIZE		VALUE		TOLERANCE		ENERGY CLASS		PACKAGING		OPTION					
MEPIA		0805		2R0		I = 7.5 % K = 10 % L = 20 % M = 30 %		L = low (typical all fire = 500 µJ) H = high (typical all fire = 1 mJ)		For more information see “Codification of packaging” table		Leave blank if no option					

CODIFICATION OF PACKAGING

CODE 18	PACKAGING	REMARK (USUAL ASSEMBLY PROCESS)
T	Tape and reel (plastic tape)	Automatic pick-and-place
W	Waffle pack	Manual placing on PCB
B	Bag	Bowl feeding



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Vishay products are not designed for use in life-saving or life-sustaining applications or any application in which the failure of the Vishay product could result in personal injury or death unless specifically qualified in writing by Vishay. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.