


Thin Film 0304 Size Resistor on Alumina



Product may not be to scale

The CC6- series single-value resistor chips offer a small size, low shunt capacitance and solder pad option. The CC6- nichrome resistors material offers excellent stability.

The CC6- resistors are manufactured using Vishay Electro-Films (EFI) sophisticated thin film equipment and manufacturing technology. The CC6- resistors are 100 % electrically tested and visually inspected to MIL-STD-883, method 2032 class H or K.

FEATURES

- Wire bondable
- Chip size: 0.030" x 0.045"
- Case: 0304
- Resistance range: 20 Ω to 59 k Ω
- Alumina substrate
- Low stray capacitance: < 0.2 pF
- Resistor material: Nichrome
- Resistor passivation coat optional
- Tolerances to 0.05 %
- Solder pad optional
- Material categorization: For definitions of compliance please see www.vishay.com/doc?99912



RoHS*
Available

HALOGEN
FREE
Available

GREEN
(5-2008)
Available

Note

* This datasheet provides information about parts that are RoHS-compliant and/or parts that are non-RoHS-compliant. For example, parts with lead (Pb) terminations are not RoHS-compliant. Please see the information/tables in this datasheet for details.

APPLICATIONS

Vishay EFI CC6- chip resistors provide excellent high-frequency response and are ideally suited for prototyping.


Typical application areas are:

- Amplifiers
- Oscillators
- Attenuators
- Couplers
- Filters

Recommended for hermetic applications where die is not exposed to moisture.


TEMPERATURE COEFFICIENT OF RESISTANCE, VALUES, AND TOLERANCES

PARAMETER	VALUE	UNIT
Total Resistance Range	20 to 59K	Ω
Standard Tolerances	± 0.05 , ± 0.1	%
TCR	± 10 , ± 25 , ± 50 , ± 100	ppm/ $^{\circ}$ C



STANDARD ELECTRICAL SPECIFICATIONS

PARAMETER	VALUE	UNIT
Noise, MIL-STD-202, Method 308	- 20 typ.	dB
Moisture Resistance, MIL-STD-202, Method 106 - Hermetic Applications	± 0.2 max. $\Delta R/R$	%
Stability, 1000 h, + 125 $^{\circ}$ C, 65 mW	± 0.1 max. $\Delta R/R$	%
Operating Temperature Range	- 55 to + 125	$^{\circ}$ C
Thermal Shock, MIL-STD-202, Method 107, Test Condition F	± 0.25 max. $\Delta R/R$	%
High Temperature Exposure, + 150 $^{\circ}$ C, 100 h	± 0.1 max. $\Delta R/R$	%
Dielectric Voltage Breakdown	400	V
Insulation Resistance	10^{12} min.	Ω
Operating Voltage	100 max.	V
DC Power Rating at + 125 $^{\circ}$ C (Derated to zero at + 150 $^{\circ}$ C)	0.065 max.	W
5 x Rated Power Short-Time Overload, + 25 $^{\circ}$ C, 5 s	± 0.25 max. $\Delta R/R$	%

DIMENSIONS in inches

SCHEMATIC


MECHANICAL SPECIFICATIONS	
PARAMETER	VALUE
Chip Size	0.030" x 0.045" $\pm$ 0.003" (0.762 mm x 1.143 mm $\pm$ 0.076 mm)
Chip Thickness	0.010" $\pm$ 0.002" (0.25 mm $\pm$ 0.05 mm)
Chip Substrate Material	99.6 % alumina, 2 μ " to 4 μ " finish
Resistor Material	Nichrome
Bonding Pad Size	0.010" x 0.024" (0.254 mm x 0.61 mm) minimum
Number of Pads	2
Pad Material	25 kÅ minimum gold standard
Backing	None

GLOBAL PART NUMBER INFORMATION																
Global Part Number: CC6-12500KKSSNHWS																
Global Part Number Description: CC6- 1.25K 10 % 100 ppm/°C Std SnPb None H WS																
C	C	6	-	1	2	5	0	0	K	K	S	S	N	H	W	S
MODEL	RESISTANCE	RESISTANCE MULTIPLIER CODE	TOL. CODE (%)	TCR (ppm/°C)	TRIM STYLE	TERMINATION	BACK METAL	VISUAL CLASS	PACKAGING CODE							
CC6-	First 4 digits are significant figures of resistance	B = 0.01 A = 0.1 0 = 1 1 = 10	A = 0.05 B = 0.1 C = 0.25 D = 0.5 F = 1.0 G = 2.0 J = 5.0 K = 10.0	E = ± 25 C = ± 50 K = ± 100	E = Edg S = Std U = Usr	G = Au S = SnPb A = Al T = Lead (Pb)-free (e1)	G = Au N = None	H = Class H K = Class K	WS = Waffle pack 100 min., 1 mult TS = Tape and reel 100 min., 1 mult							



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Vishay products are not designed for use in life-saving or life-sustaining applications or any application in which the failure of the Vishay product could result in personal injury or death unless specifically qualified in writing by Vishay. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.