


9 mm Sealed Panel Potentiometer



FEATURES

- Conductive plastic
- Industrial grade
- Wide ohmic range (1 kΩ to 1 MΩ)
- Minimal depth package: only 5 mm behind panel
- PC board and bushing mount
- Withstands typical industrial washing processes
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912


RoHS
COMPLIANT

LINKS TO ADDITIONAL RESOURCES




QUICK REFERENCE DATA


Multiple module	No
Switch module	Yes
Detent module	n/a
Special electrical laws	A: linear
Sealing level	IP 67
Lifespan	50K cycles

DIMENSIONS in millimeters (inches) ± 0.5 mm (± 0.02")



P9AC





P9AY



DIMENSIONS in millimeters (inches) ± 0.5 mm (± 0.02 ")

P9AH (with switch)

Common Dimensions


**ELECTRICAL SPECIFICATIONS**

Resistive element	Conductive plastic
Electrical travel	$270^{\circ} \pm 15^{\circ}$
Resistance range	1 k Ω to 1 M Ω (see "Standard Resistance Element Data")
Tolerance	$\pm 20\%$ (standard)
Power rating (linear)	0.25 W at +70 °C 
Circuit diagram	
Temperature coefficient	± 1000 ppm/°C
Limiting element voltage	200 V _{AC}
Contact resistance variation (typical)	1 % or 1 Ω max.
End resistance (typical)	2 % or 2 Ω max.
Dielectric strength (RMS)	900 V _{AC} (sea level) / 350 V _{AC} (70 000 feet)
Insulation resistance (500 V _{DC})	1000 M Ω min.
Independent linearity (typical)	$\pm 5\%$

MECHANICAL SPECIFICATIONS

Mechanical travel	$295^{\circ} \pm 10^{\circ}$
Operating torque (max. Ncm)	3.53 Ncm (5 oz.in.)
End stop torque	5.65 Ncm (8 oz.in.)
Mounting torque	45 Ncm (4.0 lb.in.) max. (plastic bushing)
Unit weight (max.)	4.5 g (potentiometer) / 7 g (potentiometer + switch)

ENVIRONMENTAL SPECIFICATIONS

Temperature range	-40 °C to +125 °C (-40 °F to +257 °F)
Moisture sensitivity level	1

**SWITCH OPTION**

Switch actuation angle	- Switch connection between "A" and "C" at ccw end stop - Switch connection between "C" and "B" after traveling 14° approx. at cw direction
Switching current maximum	100 mA at 16 V _{DC}
Dielectric strength	350 V _{DC}
Contact resistance	2 Ω max.
Detent torque	0.35 Ncm (0.5 oz.in. min.)
Life span	10 000 actuations
Electrical diagram: RSID single pole CHANGEOVER: in full ccw position, the contact is made between C and A, and open between C and B. Switch actuation (cw direction) reverses these positions.	

PERFORMANCE

TESTS	CONDITIONS	TYPICAL VALUES AND DRIFTS
Load life	1000 h at rated power, ambient temperature +70 °C	Total resistance shift = ± 10 %
Moisture resistance	MIL-STD-202 Method 103, Condition B	Total resistance shift = ± 10 %
Rotational life (no load)	50 000 cycles	Total resistance shift = ± 5 % Contact resistance variation = ± 3 % or ± 3 Ω, whichever is greater
Shock	100 g	Total resistance shift = ± 1 % Voltage resistance shift = ± 1 %
Vibration	30 g	Total resistance shift = ± 1 % Voltage resistance shift = ± 1 %

Note

- Nothing stated herein shall be construed as a guarantee of quality or durability

STANDARD RESISTANCE ELEMENT DATA

RESISTANCE CODE	STANDARD RESISTANCE VALUES	LINEAR LAW		
		MAX. POWER AT 70 °C	MAX. WORKING VOLTAGE	MAX. CURRENT THROUGH WIPER
	Ω	W	V	mA
102	1000	0.25	15.81	15.8
202	2000	0.25	22.36	11.2
502	5000	0.25	35.36	7.1
103	10 000	0.25	50.00	5.0
203	20 000	0.25	70.71	3.5
503	50 000	0.25	111.80	2.2
104	100 000	0.25	158.11	1.6
204	200 000	0.20	200.00	1.0
504	500 000	0.08	200.00	0.4
105	1 000 000	0.04	200.00	0.2

MARKING

Vishay trademark
Resistance code
Manufacturing date code
Model number
Product code
Terminal style

**ORDERING INFORMATION** (part number)

P	9	A	C	0	A	G	B	S	1	0	3	M	A				
MODEL	STYLE	SWITCH	BUSHING	SHAFT				END SHAFT	OHMIC VALUE		TOLERANCE	TAPER	SPECIAL NUMBER				
P9A	C Y H (only available with switch)	0 = without switch 1 = RSID	A = $\varnothing \frac{1}{4}$ " length $\frac{1}{4}$ " 0 = bushingless (board level control)		$\varnothing$	L	Bushing	S = slotted F = flattened	From 1 k Ω to 1 M Ω 103 = 10 k Ω See "Standard Resistance Element Data"		M = 20 %	A = linear	(If applicable) Given by Vishay for custom design				
				BB		12.7 mm ($\frac{1}{2}$ ")	A										
				BH	3.18 mm ($\frac{1}{8}$ ")	19.1 mm ($\frac{3}{4}$ ")	A										
				BX		5.59 mm	0										

PART NUMBER DESCRIPTION (for information only)

P9A	C	0	A	BB	Slotted	10K	20 %	Linear
MODEL	STYLE	SWITCH	BUSHING	SHAFT	END SHAFT	VALUE	TOLERANCE	TAPER

STANDARD COMBINATION OF STYLE / SWITCH / BUSHING / SHAFT

STYLE	SWITCH	BUSHING	SHAFT / END SHAFT	AVAILABLE VERSION
C	0	A	BBS	P9AC0ABBS__MA
		0	BXF	P9AC00BXF__MA
Y	0	A	BBS	P9AY0ABBS__MA
H	1		BHS	P9AH1ABHS__MA

ACCESSORIES

Additional Accessories (to order separately)	www.vishay.com/doc?51051
Control Knobs	www.vishay.com/doc?51101

RELATED DOCUMENTS

APPLICATION NOTES	
Potentiometers and Trimmers	www.vishay.com/doc?51001
Guidelines for Vishay Sfernice Resistive and Inductive Components	www.vishay.com/doc?52029



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Vishay products are not designed for use in life-saving or life-sustaining applications or any application in which the failure of the Vishay product could result in personal injury or death unless specifically qualified in writing by Vishay. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.