


Molded, 50 mil Pitch, Dual-In-Line Thin Film Resistor, Surface Mount Network



LINKS TO ADDITIONAL RESOURCES



Product Page



Packages



Footprints




Order Samples

Vishay Dale Thin Film offers standard circuits in 16 pins in a medium body molded surface mount package. The networks are available over a resistance range of 100 Ω to 100 k Ω . The network features tight ratio tolerances and close TCR tracking. In addition to the standards shown, custom circuits are available upon request.




ATTENTION!
Observe Precautions for
Handling Electrostatic Sensitive Devices!

SCHEMATIC



The 01 circuit provides 15 nominally equal resistors, each connected between a common lead (16) and a discrete PC board pin.



The 03 circuit provides a choice of 8 nominally equal resistors with each resistor isolated from all others and wired directly across.

FEATURES

- 0.090" (2.29 mm) maximum seated height
- Rugged, molded case construction (0.22" wide)
- Highly stable thin film ratio stability ($\Delta R \pm 0.015\%$ at 70 $^{\circ}\text{C}$ for 2000 h)
- Low temperature coefficient, ± 25 ppm/ $^{\circ}\text{C}$ (-55 $^{\circ}\text{C}$ to +125 $^{\circ}\text{C}$)
- Wide resistance range 100 Ω to 100 k Ω
- Isolated / bussed circuits
- Material categorization: for definitions of compliance please see www.vishay.com/doc/299912



RoHS*
Available
HALOGEN FREE

Note


* This datasheet provides information about parts that are RoHS-compliant and / or parts that are non RoHS-compliant. For example, parts with lead (Pb) terminations are not RoHS-compliant. Please see the information / tables in this datasheet for details

TYPICAL PERFORMANCE

	ABSOLUTE	TRACKING
TCR	25	5
	ABSOLUTE	RATIO
TOL.	0.1	0.025

STANDARD ELECTRICAL SPECIFICATIONS

TEST	SPECIFICATIONS	CONDITIONS
Material	Passivated nichrome	-
Pin / lead number	16	-
Resistance range	100 Ω to 100 k Ω per resistor	-
TCR: absolute	± 25 ppm/ $^{\circ}\text{C}$	-55 $^{\circ}\text{C}$ to +125 $^{\circ}\text{C}$
TCR: tracking	± 5 ppm/ $^{\circ}\text{C}$	-55 $^{\circ}\text{C}$ to +125 $^{\circ}\text{C}$
Tolerance: absolute	$\pm 0.1\%$ to $\pm 1\%$	+25 $^{\circ}\text{C}$
Tolerance: ratio	$\pm 0.025\%$ to $\pm 0.5\%$	+25 $^{\circ}\text{C}$
Power rating: resistor	50 mW = PIN 16 common 100 mW = isolated	Maximum at +70 $^{\circ}\text{C}$
Power rating: package	750 mW	Maximum at +70 $^{\circ}\text{C}$
Stability: absolute	$\Delta R \pm 0.05\%$	2000 h at +70 $^{\circ}\text{C}$
Stability: ratio	$\Delta R \pm 0.015\%$	2000 h at +70 $^{\circ}\text{C}$
Voltage coefficient	0.1 ppm/V	-
Working voltage	100 V max. not to exceed $\sqrt{P \times R}$	-
Operating temperature range	-55 $^{\circ}\text{C}$ to +125 $^{\circ}\text{C}$	-
Storage temperature range	-55 $^{\circ}\text{C}$ to +150 $^{\circ}\text{C}$	-
Noise	< -30 dB	-
Thermal EMF	0.08 $\mu\text{V}/^{\circ}\text{C}$	-
Shelf life stability: absolute	$\Delta R \pm 0.01\%$	1 year at +25 $^{\circ}\text{C}$
Shelf life stability: ratio	$\Delta R \pm 0.002\%$	1 year at +25 $^{\circ}\text{C}$

DIMENSIONS AND IMPRINTING in inches and millimeters


DIMENSION	INCHES	MILLIMETERS
A	0.350	8.89
B	0.400	10.16
C	0.440	11.176
D	0.050	1.27
E	0.018	0.457
F	0.160	4.06
G	0.08	2.03
H	0.036	0.914
J	0.22	5.59
K	0.244	6.20
L	0.30	7.52
M	0.045	1.14
N	0.003	0.076
P	0.005	1.27
Q	0.008	0.203
R	0.085	2.16
S	0.003	0.076


Note

- The tolerance and package code is NOT a member of the part marking. For space considerations the part number may be broken up, i. e.:

TOMC1603
 ▼ 1002
 ○ YYWW

MECHANICAL SPECIFICATIONS

Resistive element	Passivated nichrome
Substrate material	High purity alumina
Body	Molded epoxy
Terminals	Copper alloy
Lead (Pb)-free option	100 % matte tin
Tin lead option	Sn85
Tin lead and lead (Pb)-free finish	Plated

DERATING CURVE




GLOBAL PART NUMBER INFORMATION

New Global Part Numbering: TOMC16031002BUF

T	O	M	C	1	6	0	3	1	0	0	2	B	U	F	
T	O	M	C	T	1	6	0	1	1	0	0	3	Z	T	1
GLOBAL MODEL (4 or 5 digits)		PINS	SCHEMATIC		RESISTANCE			TOLERANCE AND RATIO TOLERANCE			PACKAGING				
TOMC (Tin lead)		16	01 = 15 bussed equal resistors		First 3 digits are significant figures and the last digit specifies the number of zeros to follow.			Abs. tol. Ratio			TAPE AND REEL				
TOMCT (Lead (Pb)-free) (e3)			03 = 8 isolated equal resistors		Example: 1002 = 10K 1003 = 100K			A = 0.1 % ⁽¹⁾ 0.05 % B = 0.1 % 0.1 % C = 0.25 % 0.1 % D = 0.5 % 0.1 % F = 1 % 0.5 % Z = 0.1 % ⁽²⁾ 0.025 %			T0 = 100 min., 100 mult. T1 = 1000 min., 1000 mult. ⁽³⁾ T3 = 300 min., 300 mult. T5 = 500 min., 500 mult. TF = full reel 2000 TS = 100 min., 1 mult.				
UF = TUBED															
Historical Part Number Example: TOMC16011002Z (for reference purposes only)															
TOMC		16		01		1002		Z							
SERIES		NUMBER OF LEADS		SCHEMATIC		RESISTANCE		TOLERANCE AND RATIO TOLERANCE							

Notes

- (1) Tolerance available 250 and up
(2) Tolerance available 1K and up
(3) Preferred packaging code



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Vishay products are not designed for use in life-saving or life-sustaining applications or any application in which the failure of the Vishay product could result in personal injury or death unless specifically qualified in writing by Vishay. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.