



Custom Thick Film Networks, Quadpack, Surface Mount




SCHEMATICS

Custom Resistor Quad



Custom Resistor/Capacitor Quad



RESISTOR SPECIFICATIONS

Resistance Range: 10 Ω to 10 M Ω , other values available on request

Resistance Tolerance: F = $\pm 1\%$, G = $\pm 2\%$, J = $\pm 5\%$ standard, tighter tolerances available

Temperature Coefficient: (- 55 $^{\circ}\text{C}$ to + 125 $^{\circ}\text{C}$) ± 100 ppm/ $^{\circ}\text{C}$ standard, ± 50 ppm/ $^{\circ}\text{C}$ available

Maximum Working Voltage: 50 V_{DC} maximum. Higher voltage available on request

FEATURES

- Thick film resistive elements
- NP0 or X7R capacitors for line terminator
- R, C, D multicomponent network
- Wide operating temperature range, - 55 $^{\circ}\text{C}$ to + 125 $^{\circ}\text{C}$
- TCR tracking = ± 50 ppm/ $^{\circ}\text{C}$
- Surface mount "J" leads or gull wing leads
- Custom resistor, capacitor and diode network combinations

CAPACITOR SPECIFICATIONS

Model: NP0 or X7R

Size: 0805 to 1210

NP0 Capacitance Range Standard: 1 pF to 0.56 μF , other values available

X7R Capacitance Range: 330 pF to 0.027 μF , other values available

Note

- NP0 capacitors may be substituted for X7R capacitors

Tolerance: NP0 = J $\pm 5\%$, K $\pm 10\%$ standard

X7R = K $\pm 10\%$, M $\pm 20\%$ standard, tighter tolerances available

Voltage Rating: 50 V_{DC}, higher voltage available on request

MECHANICAL SPECIFICATIONS


Lead: "J" lead/gull wing available.

Standard Ceramic Size: 0.5" (12.7 mm) x 0.5" (12.7 mm), 0.75" (19.05 mm) x .75" (19.05 mm), 1.0" (25.4 mm) x 1.0" (25.4 mm), 1.25" (31.75 mm) x 1.25" (31.75 mm), 1.5" (38.1 mm) x 1.5" (38.1 mm)

Note

- Parts will be covered with polymer, glass or ceramic lid

DIMENSIONS in inches (millimeters)



ORDERING INFORMATION

- For custom product information contact factory



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Vishay products are not designed for use in life-saving or life-sustaining applications or any application in which the failure of the Vishay product could result in personal injury or death unless specifically qualified in writing by Vishay. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.