

Dual N-Channel 30-V (D-S) MOSFET with Schottky Diode

PRODUCT SUMMARY

PRODUCT SUMMARY			
	V _{DS} (V)	r _{DS(on)} (Ω)	I _D (A)
Channel-1	30	0.023 at V _{GS} = 10 V	7.0
		0.032 at V _{GS} = 4.5 V	5.6
Channel-2		0.020 at V _{GS} = 10 V	7.4
		0.027 at V _{GS} = 4.5 V	6.4

SCHOTTKY PRODUCT SUMMARY

V _{DS} (V)	V _{SD} (V) Diode Forward Voltage	I _F (A)
30	0.40 V at 1.0 A	2.0

FEATURES


- LITTLE FOOT® Plus Integrated Schottky
- 100 % R_g Tested

APPLICATIONS


- Logic DC/DC
- Notebook PC



RoHS
COMPLIANT



Ordering Information: Si4914DY-T1-E3 (Lead (Pb)-free)



ABSOLUTE MAXIMUM RATINGS T_A = 25 °C, unless otherwise noted

Parameter		Symbol	Channel-1		Channel-2		Unit
			10 sec	Steady State	10 sec	Steady State	
Drain-Source Voltage		V _{DS}	30				V
Gate-Source Voltage		V _{GS}	20				
Continuous Drain Current (T _J = 150 °C) ^a	T _A = 25 °C	I _D	7.0	5.5	7.4	5.7	A
	T _A = 70 °C		5.6	4.3	6	4.5	
Pulsed Drain Current		I _{DM}	40		40		
Continuous Source Current (Diode Conduction) ^a		I _S	1.7	1.0	1.8	0.95	
Single Pulse Avalanche Current	L = 0.1 mH	I _{AS}	13		15		mJ
Avalanche Energy		E _{AS}	8.45		11		
Maximum Power Dissipation ^a	T _A = 25 °C	P _D	1.9	1.1	2.0	1.16	W
	T _A = 70 °C		1.2	0.71	1.3	0.74	
Operating Junction and Storage Temperature Range		T _J , T _{stg}	- 55 to 150				°C

THERMAL RESISTANCE RATINGS

Parameter	Symbol	Channel-1		Channel-2		Unit
		Typ	Max	Typ	Max	
Maximum Junction-to-Ambient ^a	R _{thJA}	52	65	47	60	°C/W
		90	112	85	107	
Maximum Junction-to-Foot (Drain)	R _{thJF}	30	38	28	35	

Notes:

a. Surface Mounted on 1" x 1" FR4 Board.

MOSFET SPECIFICATIONS $T_J = 25\text{ }^{\circ}\text{C}$, unless otherwise noted							
Parameter	Symbol	Test Conditions		Min	Typ ^a	Max	Unit
Static							
Gate Threshold Voltage	$V_{GS(th)}$	$V_{DS} = V_{GS}$, $I_D = 250\text{ }\mu\text{A}$	Ch-1	1.0		2.5	V
			Ch-2	1.0		2.5	
Gate-Body Leakage	I_{GSS}	$V_{DS} = 0\text{ V}$, $V_{GS} = 20\text{ V}$	Ch-1			100	nA
			Ch-2			100	
Zero Gate Voltage Drain Current	I_{DSS}	$V_{DS} = 30\text{ V}$, $V_{GS} = 0\text{ V}$	Ch-1			1	μA
			Ch-2			500	
		$V_{DS} = 30\text{ V}$, $V_{GS} = 0\text{ V}$, $T_J = 85\text{ }^{\circ}\text{C}$	Ch-1			0.015	mA
			Ch-2			20	
On-State Drain Current ^b	$I_{D(on)}$	$V_{DS} = 5\text{ V}$, $V_{GS} = 10\text{ V}$	Ch-1	20			A
			Ch-2	20			
Drain-Source On-State Resistance ^b	$r_{DS(on)}$	$V_{GS} = 10\text{ V}$, $I_D = 7.0\text{ A}$	Ch-1		0.019	0.023	Ω
		$V_{GS} = 10\text{ V}$, $I_D = 7.4\text{ A}$	Ch-2		0.016	0.020	
		$V_{GS} = 4.5\text{ V}$, $I_D = 5.6\text{ A}$	Ch-1		0.026	0.032	
		$V_{GS} = 4.5\text{ V}$, $I_D = 6.4\text{ A}$	Ch-2		0.022	0.027	
Forward Transconductance ^b	g_{fs}	$V_{DS} = 15\text{ V}$, $I_D = 7.0\text{ A}$	Ch-1		19		S
		$V_{DS} = 15\text{ V}$, $I_D = 7.4\text{ A}$	Ch-2		22		
Diode Forward Voltage ^b	V_{SD}	$I_S = 1.7\text{ A}$, $V_{GS} = 0\text{ V}$	Ch-1		0.75	1.1	V
		$I_S = 1\text{ A}$, $V_{GS} = 0\text{ V}$	Ch-2		0.36	0.40	
Dynamic ^a							
Total Gate Charge	Q_g	Channel-1 $V_{DS} = 15\text{ V}$, $V_{GS} = 4.5\text{ V}$, $I_D = 7.0\text{ A}$ Channel-2 $V_{DS} = 15\text{ V}$, $V_{GS} = 4.5\text{ V}$, $I_D = 7.4\text{ A}$	Ch-1		5.6	8.5	nC
Gate-Source Charge	Q_{gs}		Ch-2		7.3	11	
			Ch-1		2.3		
Gate-Drain Charge	Q_{gd}		Ch-2		2.8		
		Ch-1		1.7			
			Ch-2		2.2		
Gate Resistance	R_g		Ch-1	0.5	2.3	3.6	Ω
			Ch-2	0.5	1.6	2.5	
Turn-On Delay Time	$t_{d(on)}$	Channel-1 $V_{DD} = 15\text{ V}$, $R_L = 15\text{ }\Omega$ $I_D \equiv 1\text{ A}$, $V_{GEN} = 10\text{ V}$, $R_g = 6\text{ }\Omega$ Channel-2 $V_{DD} = 15\text{ V}$, $R_L = 15\text{ }\Omega$ $I_D \equiv 1\text{ A}$, $V_{GEN} = 10\text{ V}$, $R_g = 6\text{ }\Omega$	Ch-1		6	10	ns
Rise Time	t_r		Ch-2		7	11	
			Ch-1		13	20	
Turn-Off Delay Time	$t_{d(off)}$		Ch-2		13	20	
		Ch-1		27	40		
Fall Time	t_f	Ch-2		35	53		
		Ch-1		9	15		
Source-Drain Reverse Recovery Time	t_{rr}	Ch-2		10	15		
			$I_F = 1.3\text{ A}$, $di/dt = 100\text{ A}/\mu\text{s}$	Ch-1		30	50
			$I_F = 2.2\text{ A}$, $di/dt = 100\text{ }\mu\text{A}/\mu\text{s}$	Ch-2		30	50

Notes:


a. Guaranteed by design, not subject to production testing.

b. Pulse test; pulse width $\leq 300\text{ }\mu\text{s}$, duty cycle $\leq 2\%$.


SCHOTTKY SPECIFICATIONS $T_J = 25\text{ }^{\circ}\text{C}$, unless otherwise noted							
Parameter	Symbol	Test Conditions		Min	Typ	Max	Unit
Forward Voltage Drop	V_F	$I_F = 1.0\text{ A}$			0.36	0.40	V
		$I_F = 1.0\text{ A}$, $T_J = 150\text{ }^{\circ}\text{C}$			0.27	0.31	
Maximum Reverse Leakage Current	I_{rm}	$V_r = 30\text{ V}$			0.008	0.50	mA
		$V_r = 30\text{ V}$, $T_J = 100\text{ }^{\circ}\text{C}$			3.5	10	
		$V_r = -30\text{ V}$, $T_J = 125\text{ }^{\circ}\text{C}$			10	100	
Junction Capacitance	C_T	$V_r = 10\text{ V}$			58		pF

Stresses beyond those listed under "Absolute Maximum Ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated in the operational sections of the specifications is not implied. Exposure to absolute maximum rating conditions for extended periods may affect device reliability.


CHANNEL-1 TYPICAL CHARACTERISTICS 25 °C, unless noted




Output Characteristics




Transfer Characteristics




On-Resistance vs. Drain Current




Capacitance




Gate Charge




On-Resistance vs. Junction Temperature

CHANNEL-1 TYPICAL CHARACTERISTICS 25 °C, unless noted


Source-Drain Diode Forward Voltage




On-Resistance vs. Gate-to-Source Voltage




Threshold Voltage




Single Pulse Power, Junction-to-Ambient









CHANNEL-1 TYPICAL CHARACTERISTICS 25 °C, unless noted




Normalized Thermal Transient Impedance, Junction-to-Ambient




Normalized Thermal Transient Impedance, Junction-to-Foot

CHANNEL-2 TYPICAL CHARACTERISTICS 25 °C, unless noted


CHANNEL-2 TYPICAL CHARACTERISTICS 25 °C, unless noted




Source-Drain Diode Forward Voltage




On-Resistance vs. Gate-to-Source Voltage





Reverse Current vs. Junction Temperature



Single Pulse Power, Junction-to-Ambient



CHANNEL-2 TYPICAL CHARACTERISTICS 25 °C, unless noted

Vishay Siliconix maintains worldwide manufacturing capability. Products may be manufactured at one of several qualified locations. Reliability data for Silicon Technology and Package Reliability represent a composite of all qualified locations. For related documents such as package/tape drawings, part marking, and reliability data, see <http://www.vishay.com/ppg?72938>.



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Vishay products are not designed for use in life-saving or life-sustaining applications or any application in which the failure of the Vishay product could result in personal injury or death unless specifically qualified in writing by Vishay. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.