

P-Channel 1.5-V (G-S) MOSFET

PRODUCT SUMMARY			
V _{DS} (V)	r _{DS(on)} (Ω)	I _D (A) ^a	Q _g (Typ)
- 8	0.035 at V _{GS} = - 4.5 V	- 11.7	21 nC
	0.042 at V _{GS} = - 2.5 V	- 10.7	
	0.052 at V _{GS} = - 1.8 V	- 9.6	
	0.069 at V _{GS} = - 1.5 V	- 8.3	

FEATURES

- TrenchFET[®] Power MOSFET
- Industry First 1.5 V Rated MOSFET
- Ultra Small MICRO FOOT[®] Chip-scale Packaging Reduces Footprint Area, Profile (0.62 mm) and On-Resistance Per Footprint Area




RoHS
COMPLIANT


APPLICATIONS

- Low Threshold Load Switch for Portable Devices
 - Low Power Consumption
 - Increased Battery Life

MICRO FOOT



Ordering Information: Si8419DB-T1-E1



P-Channel MOSFET

ABSOLUTE MAXIMUM RATINGS T _A = 25 °C, unless otherwise noted				
Parameter		Symbol	Limit	Unit
Drain-Source Voltage		V _{DS}	- 8	V
Gate-Source Voltage		V _{GS}	± 5	
Continuous Drain Current (T _J = 150 °C)	T _C = 25 °C	I _D	- 11.7	A
	T _C = 70 °C		- 9.4	
	T _A = 25 °C		- 7.8 ^{b, c}	
	T _A = 70 °C		- 6.3 ^{b, c}	
Pulsed Drain Current		I _{DM}	- 25	
Continuous Source-Drain Diode Current	T _C = 25 °C	I _S	- 5.7	
	T _A = 25 °C		- 2.5 ^{b, c}	
Maximum Power Dissipation	T _C = 25 °C	P _D	6.25	W
	T _C = 70 °C		4	
	T _A = 25 °C		2.77 ^{b, c}	
	T _A = 70 °C		1.77 ^{b, c}	
Operating Junction and Storage Temperature Range		T _J , T _{stg}	- 55 to 150	°C
Package Reflow Conditions ^d	VPR		260	
	IR/Convection		260	

Notes:

a. Based on T_C = 25 °C.

b. Surface Mounted on 1" x 1" FR4 Board.

c. t = 10 sec.

d. Refer to IPC/JEDEC (J-STD-020C), no manual or hand soldering.

e. In this document, any reference to the Case represents the body of the MICRO FOOT device and Foot is the bump.

THERMAL RESISTANCE RATINGS

Parameter	Symbol	Typical	Maximum	Unit
Maximum Junction-to-Ambient ^{a, b}	R_{thJA}	35	45	°C/W
Maximum Junction-to-Foot (Drain)	Steady State R_{thJB}	16	20	

Notes:

a. Surface Mounted on 1" x 1" FR4 Board.

b. Maximum under Steady State conditions is 85 °C/W.

SPECIFICATIONS $T_J = 25\text{ °C}$, unless otherwise noted

Parameter	Symbol	Test Conditions	Min	Typ	Max	Unit
Static						
Drain-Source Breakdown Voltage	V_{DS}	$V_{GS} = 0\text{ V}, I_D = -250\text{ }\mu\text{A}$	- 8			V
V_{DS} Temperature Coefficient	$\Delta V_{DS}/T_J$	$I_D = -250\text{ }\mu\text{A}$		- 7.5		mV/°C
$V_{GS(th)}$ Temperature Coefficient	$\Delta V_{GS(th)}/T_J$			- 2.2		
Gate-Source Threshold Voltage	$V_{GS(th)}$	$V_{DS} = V_{GS}, I_D = -250\text{ }\mu\text{A}$	- 0.35		- 0.8	V
		$V_{DS} = V_{GS}, I_D = -5\text{ mA}$		- 0.6		
Gate-Source Leakage	I_{GSS}	$V_{DS} = 0\text{ V}, V_{GS} = 5\text{ V}$			- 100	nA
Zero Gate Voltage Drain Current	I_{DSS}	$V_{DS} = 8\text{ V}, V_{GS} = 0\text{ V}$			- 1	μA
		$V_{DS} = -8\text{ V}, V_{GS} = 0\text{ V}, T_J = 70\text{ °C}$			- 10	
On-State Drain Current ^a	$I_{D(on)}$	$V_{DS} \leq 5\text{ V}, V_{GS} = -4.5\text{ V}$	- 5			A
Drain-Source On-State Resistance ^a	$r_{DS(on)}$	$V_{GS} = -4.5\text{ V}, I_D = -1\text{ A}$		0.029	0.035	Ω
		$V_{GS} = -2.5\text{ V}, I_D = -1\text{ A}$		0.035	0.042	
		$V_{GS} = -1.8\text{ V}, I_D = -1\text{ A}$		0.043	0.052	
		$V_{GS} = -1.5\text{ V}, I_D = -1\text{ A}$		0.051	0.069	
Forward Transconductance ^a	g_{fs}	$V_{DS} = -4\text{ V}, I_D = -1\text{ A}$		0.7	1.2	S
Dynamic^b						
Input Capacitance	C_{iss}	$V_{DS} = -4\text{ V}, V_{GS} = 0\text{ V}, f = 1\text{ MHz}$		1640		pF
Output Capacitance	C_{oss}			590		
Reverse Transfer Capacitance	C_{rss}			380		
Total Gate Charge	Q_g	$V_{DS} = -4\text{ V}, V_{GS} = -5\text{ V}, I_D = -1\text{ A}$		24	26	nC
		$V_{DS} = -4\text{ V}, V_{GS} = -4.5\text{ V}, I_D = 1\text{ A}$		21	32	
Gate-Source Charge	Q_{gs}			1.8		
Gate-Drain Charge	Q_{gd}			3.7		
Gate Resistance	R_g	$V_{GS} = -0.1\text{ V}, f = 1\text{ MHz}$		22		Ω
Turn-On Delay Time	$t_{d(on)}$	$V_{DD} = -4\text{ V}, R_L = 4\text{ }\Omega$ $I_D \cong -1\text{ A}, V_{GEN} = -4.5\text{ V}, R_g = 6\text{ }\Omega$		12	20	ns
Rise Time	t_r			25	40	
Turn-Off Delay Time	$t_{d(off)}$			260	390	
Fall Time	t_f			155	240	









SPECIFICATIONS $T_J = 25\text{ }^{\circ}\text{C}$, unless otherwise noted						
Parameter	Symbol	Test Conditions	Min	Typ	Max	Unit
Drain-Source Body Diode Characteristics						
Continuous Source-Drain Diode Current	I_S	$T_C = 25\text{ }^{\circ}\text{C}$			- 2.5	A
Pulse Diode Forward Current	I_{SM}				- 25	
Body Diode Voltage	V_{SD}	$I_S = -1\text{ A}$, $V_{GS} = 0\text{ V}$		- 0.7	- 1.1	V
Body Diode Reverse Recovery Time	t_{rr}	$I_F = -1\text{ A}$, $di/dt = 100\text{ A}/\mu\text{s}$, $T_J = 25\text{ }^{\circ}\text{C}$		150	250	ns
Body Diode Reverse Recovery Charge	Q_{rr}			0.15	0.23	nC
Reverse Recovery Fall Time	t_a			57		ns
Reverse Recovery Rise Time	t_b			93		

Notes:






- a. Pulse test; pulse width $\leq 300\text{ }\mu\text{s}$, duty cycle $\leq 2\%$.
b. Guaranteed by design, not subject to production testing.


Stresses beyond those listed under "Absolute Maximum Ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated in the operational sections of the specifications is not implied. Exposure to absolute maximum rating conditions for extended periods may affect device reliability.

TYPICAL CHARACTERISTICS 25 °C unless noted**Output Characteristics****Transfer Characteristics****On-Resistance vs. Drain Current and Gate Voltage****Capacitance****Gate Charge****On-Resistance vs. Junction Temperature**





TYPICAL CHARACTERISTICS 25 °C unless noted




TYPICAL CHARACTERISTICS 25 °C unless noted

*The power dissipation P_D is based on $T_{J(max)} = 150\text{ }^{\circ}\text{C}$, using junction-to-case thermal resistance, and is more useful in settling the upper dissipation limit for cases where additional heatsinking is used. It is used to determine the current rating, when this rating falls below the package limit.



PACKAGE OUTLINE

MICRO FOOT: 4-BUMP (2 X 2, 0.8 mm PITCH)



NOTES (Unless Otherwise Specified):

1. Laser mark on the silicon die back, coated with a thin metal.
2. Bumps are Sn/Ag/Cu.
3. Non-solder mask defined copper landing pad.
4. The flat side of wafers is oriented at the bottom.

Dim	MILLIMETERS*		INCHES	
	Min	Max	Min	Max
A	0.600	0.650	0.0236	0.0256
A ₁	0.260	0.290	0.0102	0.0114
A ₂	0.340	0.360	0.0134	0.0142
b	0.370	0.410	0.0146	0.0161
D	1.520	1.600	0.0598	0.0630
E	1.520	1.600	0.0598	0.0630
e	0.750	0.850	0.0295	0.0335
S	0.370	0.380	0.0146	0.0150

* Use millimeters as the primary measurement.

Vishay Siliconix maintains worldwide manufacturing capability. Products may be manufactured at one of several qualified locations. Reliability data for Silicon Technology and Package Reliability represent a composite of all qualified locations. For related documents such as package/tape drawings, part marking, and reliability data, see <http://www.vishay.com/ppg?73310>.



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Vishay products are not designed for use in life-saving or life-sustaining applications or any application in which the failure of the Vishay product could result in personal injury or death unless specifically qualified in writing by Vishay. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.