


Common - Drain Dual N-Channel 60 V (S1-S2) MOSFET

PowerPAK® 1212-8SCD



RoHS
COMPLIANT
HALOGEN
FREE

FEATURES

- TrenchFET® Gen IV power MOSFET
- Very low source-to-source on resistance
- Integrated common-drain n-channel MOSFETs in a compact and thermally enhanced package
- 100 % R_g and UIS tested
- Optimizes circuit layout for bi-directional current flow
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912

APPLICATIONS

- Battery protection switch
- Bi-directional switch
- Load switch
- 24 V systems



PRODUCT SUMMARY

V_{S1S2} (V)	60
$R_{S1S2(on)}$ max. (Ω) at $V_{GS} = 10$ V	0.0130
$R_{S1S2(on)}$ max. (Ω) at $V_{GS} = 4.5$ V	0.0185
Q_g typ. (nC)	10.2 ^g
I_{S1S2} (A)	52 ^a
Configuration	Common - Drain

ORDERING INFORMATION

Package	PowerPAK 1212-8SCD
Lead (Pb)-free and halogen-free	SiSF20DN-T1-GE3

ABSOLUTE MAXIMUM RATINGS ($T_A = 25$ °C, unless otherwise noted)

PARAMETER	SYMBOL	LIMIT	UNIT
Drain-source voltage	V_{S1S2}	60	V
Gate-source voltage	V_{GS}	± 20	V
Continuous drain current ($T_J = 150$ °C)	$T_C = 25$ °C	52	A
	$T_C = 70$ °C	41	
	$T_A = 25$ °C	14 ^{b, c}	
	$T_A = 70$ °C	11 ^{b, c}	
Pulsed drain current ($t = 100$ μ s)	I_{S1S2M}	100	
Maximum power dissipation	$T_C = 25$ °C	69.4	W
	$T_C = 70$ °C	44.4	
	$T_A = 25$ °C	5.2 ^{b, c}	
	$T_A = 70$ °C	3.3 ^{b, c}	
Operating junction and storage temperature range	T_J, T_{stg}	-55 to +150	°C
Soldering recommendations (peak temperature) °		260	

THERMAL RESISTANCE RATINGS

PARAMETER	SYMBOL	TYPICAL	MAXIMUM	UNIT
Maximum junction-to-ambient ^b	R_{thJA}	19	24	°C/W
Maximum junction-to-case (drain)	R_{thJC}	1.4	1.8	

Notes

- $T_C = 25$ °C
- Surface mounted on 1" x 1" FR4 board
- $t = 10$ s
- See solder profile (www.vishay.com/doc?73257). The PowerPAK 1212-8SCD is a leadless package. The end of the lead terminal is exposed copper (not plated) as a result of the singulation process in manufacturing. A solder fillet at the exposed copper tip cannot be guaranteed and is not required to ensure adequate bottom side solder interconnection
- Rework conditions: manual soldering with a soldering iron is not recommended for leadless components
- Maximum under steady state conditions is 63 °C/W
- Single MOSFET



SPECIFICATIONS (T _J = 25 °C, unless otherwise noted)						
PARAMETER	SYMBOL	TEST CONDITIONS	MIN.	TYP.	MAX.	UNIT
Static						
Drain-source breakdown voltage	V _{DS}	V _{GS} = 0 V, I _D = 250 μA	60	-	-	V
Gate-source threshold voltage	V _{GS(th)}	V _{S1S2} = V _{GS} , I _D = 250 μA	1	-	3	
Gate-source leakage	I _{GSS}	V _{S1S2} = 0 V, V _{GS} = ± 20 V	-	-	± 100	nA
Zero gate voltage drain current	I _{DSS}	V _{S1S2} = 60 V, V _{GS} = 0 V	-	-	1	μA
		V _{S1S2} = 60 V, V _{GS} = 0 V, T _J = 70 °C	-	-	15	
On-state drain current ^a	I _{S1S2(on)}	V _{S1S2} ≥ 10 V, V _{GS} = 10 V	20	-	-	A
Drain-source on-state resistance ^a	R _{S1S2(on)}	V _{GS} = 10 V, I _{S1S2} = 7 A	-	0.0100	0.0130	Ω
		V _{GS} = 4.5 V, I _{S1S2} = 5 A	-	0.0140	0.0185	
Forward transconductance ^a	g _{fs}	V _{S1S2} = 10 V, I _{S1S2} = 25 A	-	75	-	S
Dynamic ^{b, c}						
Input capacitance	C _{iss}	V _{DS} = 30 V, V _{GS} = 0 V, f = 1 MHz	-	1290	-	pF
Output capacitance	C _{oss}		-	340	-	
Reverse transfer capacitance	C _{rss}		-	8	-	
Total gate charge	Q _g	V _{DS} = 30 V, V _{GS} = 10 V, I _D =5 A	-	22	33	nC
		V _{DS} = 30 V, V _{GS} = 4.5 V, I _D = 5 A	-	10.2	16	
Q _{gs}	-		3.9	-		
Q _{gd}	-		2.9	-		
Gate resistance	R _g	f = 1 MHz	0.14	0.7	1.4	Ω
Turn-on delay time	t _{d(on)}	V _{DD} = 30 V, R _L = 6 Ω, I _{S1S2} ≅ 5 A, V _{GEN} = 10 V, R _g = 1 Ω	-	10	20	ns
Rise time	t _r		-	5	10	
Turn-off delay time	t _{d(off)}		-	19	40	
Fall time	t _f		-	5	10	
Turn-on delay time	t _{d(on)}	V _{DD} = 30 V, R _L = 6 Ω, I _D ≅ 5 A, V _{GEN} = 4.5 V, R _g = 1 Ω	-	15	30	
Rise time	t _r		-	50	100	
Turn-off delay time	t _{d(off)}		-	24	50	
Fall time	t _f		-	7	15	
Drain-Source Body Diode Characteristics ^c						
Continuous source-drain diode current	I _{S1S2}	T _C = 25 °C	-	-	52	A
Pulse diode forward current	I _{S1S2M}		-	-	100	
Body diode reverse recovery time	t _{rr}	I _F = 5 A, di/dt = 100 A/μs, T _J = 25 °C	-	30	60	ns
Body diode reverse recovery charge	Q _{rr}		-	18	35	nC
Reverse recovery fall time	t _a		-	15	-	ns
Reverse recovery rise time	t _b		-	15	-	


Notes

- a. Pulse test; pulse width $\leq 300\text{ }\mu\text{s}$, duty cycle $\leq 2\%$
b. Guaranteed by design, not subject to production testing
c. On single MOSFET


Stresses beyond those listed under "Absolute Maximum Ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated in the operational sections of the specifications is not implied. Exposure to absolute maximum rating conditions for extended periods may affect device reliability.




TYPICAL CHARACTERISTICS (25 °C, unless otherwise noted)




Output Characteristics




Transfer Characteristics




On-Resistance vs. Source Current and Gate Voltage



Capacitance




Gate Charge




On-Resistance vs. Junction Temperature




TYPICAL CHARACTERISTICS (25 °C, unless otherwise noted)




Source-Drain Diode Forward Voltage



Threshold Voltage




On-Resistance vs. Gate-to-Source Voltage




Single Pulse Power, Junction-to-Ambient




TYPICAL CHARACTERISTICS (25 °C, unless otherwise noted)



Safe Operating Area, Junction-to-Ambient



Current Derating ^b




Power, Junction-to-Case

Notes


- $V_{GS} >$ minimum V_{GS} at which $R_{DS(on)}$ is specified
- The power dissipation P_D is based on $T_J \text{ max.} = 150 \text{ °C}$, using junction-to-case thermal resistance, and is more useful in settling the upper dissipation limit for cases where additional heatsinking is used. It is used to determine the current rating, when this rating falls below the package limit



TYPICAL CHARACTERISTICS (25 °C, unless otherwise noted)



Normalized Thermal Transient Impedance, Junction-to-Ambient




Normalized Thermal Transient Impedance, Junction-to-Case

Vishay Siliconix maintains worldwide manufacturing capability. Products may be manufactured at one of several qualified locations. Reliability data for Silicon Technology and Package Reliability represent a composite of all qualified locations. For related documents such as package / tape drawings, part marking, and reliability data, see www.vishay.com/ppg?76915.




PowerPAK® 1212-8S CD with Flip Chip



DIM.	MILLIMETERS			INCHES		
	MIN.	NOM.	MAX.	MIN.	NOM.	MAX.
A	0.70	0.75	0.80	0.027	0.029	0.031
A1	0	0.02	0.05	0	0.001	0.002
b	0.27	0.32	0.37	0.011	0.013	0.015
c	-	0.20 ref.	-	-	0.008 ref.	-
D	3.20	3.30	3.40	0.126	0.130	0.134
D1	1.76	1.86	1.96	0.069	0.073	0.077
E	3.20	3.30	3.40	0.126	0.130	0.134
E1	1.18	1.28	1.38	0.046	0.050	0.054
e	0.60	0.65	0.70	0.024	0.026	0.028
K	0.50 typ.			0.020 typ.		
K1	0.35 typ.			0.014 typ.		
H	0.10	0.20	0.30	0.006	0.008	0.010
L	0.84	0.94	1.04	0.033	0.037	0.041
ECN: C17-1732-Rev. A, 18-Dec-17						
DWG: 6061						

Recommended Land Pattern





Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Vishay products are not designed for use in life-saving or life-sustaining applications or any application in which the failure of the Vishay product could result in personal injury or death unless specifically qualified in writing by Vishay. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.