

Powered-Off Protection, 0.85 Ω , 1.8 V to 5.5 V, SPDT Analog Switch (2:1 Multiplexer)

DESCRIPTION

The DG2001E is a high performance single-pole, double-throw (SPDT) analog switch designed for 1.8 V to 5.5 V operation with a single power rail.

Fabricated with high density CMOS technology, the device achieves low on resistance of 0.85 Ω at a 5 V power supply, low power consumption, and fast switching speeds.

The DG2001E can handle both analog and digital signals and permits signals with amplitudes of up to V_+ to be transmitted in either direction. Its control logic inputs can go over V_+ up to 5.5 V. The control logic input high threshold is guaranteed as low as 1.8 V over the power supply range up to 5.5 V. It features break before make switching performance.

A powered-off protection circuit is built into the switch to prevent an abnormal current flow from COM pin to V_+ during the power-down condition. Each output pin can withstand greater than 7 kV (human body model).

Operation temperature is specified from -40 $^{\circ}\text{C}$ to +85 $^{\circ}\text{C}$. The DG2001E is available in TSOP-6 package.

FEATURES

- Low switch on-resistance (0.85 Ω)
- 1.8 V to 5.5 V single supply operation
- Isolation in powered-off mode
- Guaranteed 1.8 V logic high
- Control logic inputs can go over V_+
- Low charge injection (8 pC)
- Break before make switching
- Latch-up performance exceeds 300 mA per JESD 78
- ESD tested
 - 7000 V human body model (JS-001)
 - 1000 V charge device model (JS-002)
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912





RoHS
COMPLIANT
HALOGEN
FREE


APPLICATIONS

- Consumer and computing
- Portable instrumentation
- Medical equipment
- Battery operated systems

FUNCTIONAL BLOCK DIAGRAM AND PIN CONFIGURATION



TRUTH TABLE		
LOGIC	NC	NO
0	On	Off
1	Off	On



ORDERING INFORMATION			
TEMP RANGE	PACKAGE	PART NUMBER	MARKING CODE
-40 $^{\circ}\text{C}$ to +85 $^{\circ}\text{C}$	TSOP-6	DG2001EDV-T1-GE3	H1
		DG2006EDV-T1-GE3	I1

**ABSOLUTE MAXIMUM RATINGS** ($T_A = 25\text{ }^{\circ}\text{C}$, unless otherwise noted)

PARAMETER		LIMIT	UNIT
V_+ , COM, NC, NO, IN reference to GND		-0.3 to 6	V
Continuous current (any terminal)		± 50	mA
Peak current (pulsed at 1 ms, 10 % duty cycle)		± 200	
Storage temperature (D suffix)		-65 to +125	$^{\circ}\text{C}$
Power dissipation (packages) ^a	TSOP-6 ^b	570	mW
ESD / HBM	JS-001	7000	V
ESD / CDM	JS-002	1000	
Latch up	Per JESD78 with 1.5 x voltage clamp	300	mA

Notes

- a. All leads welded or soldered to PC board
b. Derate 7 mW/ $^{\circ}\text{C}$ above 25 $^{\circ}\text{C}$

Stresses beyond those listed under "Absolute Maximum Ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated in the operational sections of the specifications is not implied. Exposure to absolute maximum rating conditions for extended periods may affect device reliability.

SPECIFICATIONS ($V_+ = 5\text{ V}$)

PARAMETER	SYMBOL	TEST CONDITIONS UNLESS OTHERWISE SPECIFIED V+ = 5 V, ± 10 % VIN = 0.8 V or 2.4 V ^e	TEMP. ^a	LIMITS -40 °C to +85 °C			UNIT
				MIN. ^b	TYP. ^c	MAX. ^b	
Analog Switch							
Analog signal range ^d	VNO, VNC VCOM		Full	0	-	V+	V
On-resistance	RON	V+ = 4.5 V VCOM = 3 V, INO, INC = 10 mA	Room	-	0.85	1.6	Ω
			Full	-	-	1.8	
RON flatness ^d	RON Flatness	V+ = 4.5 V VCOM = 0 V to V+, INO, INC = 10 mA	Room	-	0.3	-	
Switch off leakage current ^g	INO(off) INC(off)	V+ = 5.5 V VNO, VNC = 1 V / 4.5 V, VCOM = 4.5 V / 1 V	Room	-5	-	5	nA
			Full	-30	-	30	
	ICOM(off)		Room	-5	-	5	
			Full	-30	-	30	
Channel-on leakage current ^g	ICOM(on)	V+ = 5.5 V VNO, VNC = VCOM = 1 V / 4.5 V	Room	-5	-	5	
			Full	-30	-	30	
Power down leakage	ICOM(PD)	V+ = 0 V, VCOM = 4.5 V, VIN = GND	Full ^d	-	-	1	μA
Digital Control							
Input high voltage	VINH		Full	2.4	-	-	V
Input low voltage	VINL		Full	-	-	0.8	
Input capacitance	CIN		Full	-	3	-	pF
Input current	IINL or IINH	VIN = 0 V or V+	Full	-1	-	1	μA
Dynamic Characteristics							
Turn-on time	tON	VNO or VNC = 3 V, RL = 300 Ω, CL = 35 pF	Room	-	15	32	ns
			Full	-	-	35	
Turn-off time	tOFF		Room	-	6	26	
			Full	-	-	31	
Break-before-make time	td		Room	1	4	-	
Charge injection ^d	QINJ	CL = 1 nF, VGEN = 0 V, RGEN = 0 Ω	Room	-	8	-	pC
Off-isolation ^d	OIRR	RL = 50 Ω, CL = 5 pF, f = 1 MHz	Room	-	-63	-	dB
Crosstalk ^d	XTALK		Room	-	-63	-	
Source-off capacitance ^d	CNO(off) CNC(off)	VIN = 0 V or V+, f = 1 MHz	Room	-	16	-	pF
Channel-on capacitance ^d	CON		Room	-	53	-	
Power Supply							
Power supply current	I+	VIN = 0 V or V+	Full	-	0.0003	1	μA



SPECIFICATIONS (V+ = 3 V)							
PARAMETER	SYMBOL	TEST CONDITIONS UNLESS OTHERWISE SPECIFIED V+ = 3 V, ± 10 % VIN = 0.4 V or 2 V ^e	TEMP. ^a	LIMITS -40 °C to +85 °C			UNIT
				MIN. ^b	TYP. ^c	MAX. ^b	
Analog Switch							
Analog signal range ^d	VNO, VNC, VCOM		Full	0	-	V+	V
On-resistance	RON	V+ = 2.7 V VCOM = 1.5 V, INO, INC = 10 mA	Room	-	1.6	2.2	Ω
			Full	-	-	2.6	
RON flatness ^d	RON Flatness	V+ = 2.7 V VCOM = 0 V to V+, INO, INC = 10 mA	Room	-	0.6	-	nA
Switch off leakage current ^g	INO(off) INC(off)	V+ = 3.3 V VNO, VNC = 1 V / 3 V, VCOM = 3 V / 1 V	Room	-5	-	5	
			Full	-15	-	15	
	ICOM(off)		Room	-5	-	5	
			Full	-15	-	15	
Channel-on leakage current ^g	ICOM(on)	V+ = 3.3 V VNO, VNC = VCOM = 1 V / 3 V	Room	-5	-	5	
			Full	-15	-	15	
Digital Control							
Input high voltage	VINH		Full	2	-	-	V
Input low voltage	VINL		Full	-	-	0.4	
Input capacitance	CIN		Full	-	-	-	pF
Input current	IINL or INIH	VIN = 0 V or V+	Full	-1	-	1	μA
Dynamic Characteristics							
Turn-on time	tON	VNO or VNC = 2 V, RL = 300 Ω, CL = 35 pF	Room	-	21	42	ns
			Full	-	-	47	
Turn-off time	tOFF		Room	-	9	32	
			Full	-	-	35	
Break-before-make time	td		Room	1	7	-	
Charge injection ^d	QINJ	CL = 1 nF, VGEN = 0 V, RGEN = 0 Ω	Room	-	6	-	pC
Off-isolation ^d	OIRR	RL = 50 Ω, CL = 5 pF, f = 1 MHz	Room	-	-63	-	dB
Crosstalk ^d	XTALK		Room	-	-63	-	
NO, NC off capacitance ^d	CNO(off) CNC(off)	VIN = 0 V or V+, f = 1 MHz	Room	-	16	-	pF
Channel-on capacitance ^d	CON		Room	-	54	-	
Power Supply							
Power supply current	I+	VIN = 0 V or V+	Full	-	0.00002	1	μA




SPECIFICATIONS (V+ = 2 V)							
PARAMETER	SYMBOL	TEST CONDITIONS UNLESS OTHERWISE SPECIFIED V+ = 2 V, ± 10 % VIN = 0.4 V or 1.6 V ^e	TEMP. ^a	LIMITS -40 °C to +85 °C			UNIT
				MIN. ^b	TYP. ^c	MAX. ^b	
Analog Switch							
Analog signal range ^d	VNO, VNC VCOM		Full	0	-	V+	V
On-resistance	RON	V+ = 1.8 V VCOM = 1 V, INO, INC = 10 mA	Room	-	6	8	Ω
			Full	-	-	10	
RON flatness ^d	RON Flatness	V+ = 1.8 V VCOM = 0 V to V+, INO, INC = 10 mA	Room	-	6	-	
Switch off leakage current ^g	INO(off) INC(off)	V+ = 2.2 V VNO, VNC = 0.5 V / 1.5 V, VCOM = 1.5 V / 0.5 V	Room	-0.5	-	0.5	nA
			Full	-5	-	5	
	ICOM(off)		Room	-0.5	-	0.5	
			Full	-5	-	5	
Channel-on leakage current ^g	ICOM(on)	V+ = 2.2 V VNO, VNC = VCOM = 0.5 V / 1.5 V	Room	-0.5	-	0.5	
			Full	-5	-	5	
Digital Control							
Input high voltage	VINH		Full	1.6	-	-	V
Input low voltage	VINL		Full	-	-	0.4	
Input capacitance	CIN		Full	-	3	-	pF
Input current	IINL or IINH	VIN = 0 V or V+	Full	-1	-	1	μA
Dynamic Characteristics							
Turn-on time	tON	VNO or VNC = 1.5 V, RL = 300 Ω, CL = 35 pF	Room	-	36	51	ns
			Full	-	-	62	
Turn-off time	tOFF		Room	-	16	40	
			Full	-	-	43	
Break-before-make time	td		Room	1	16	-	
Charge injection ^d	QINJ		CL = 1 nF, VGEN = 0 V, RGEN = 0 Ω	Room	-	21	-
Off-isolation ^d	OIRR	RL = 50 Ω, CL = 5 pF, f = 1 MHz	Room	-	-63	-	dB
Crosstalk ^d	XTALK		Room	-	-63	-	
NO, NC off capacitance ^d	CNO(off) CNC(off)	VIN = 0 V or V+, f = 1 MHz	Room	-	16	-	pF
Channel-on capacitance ^d	CON		Room	-	52	-	
Power Supply							
Power supply current	I+	VIN = 0 V or V+	Full	-	0.00001	1	μA

Notes


- Room = 25 °C, full = as determined by the operating suffix
- The algebraic convention whereby the most negative value is a minimum and the most positive a maximum, is used in this datasheet
- Typical values are for design aid only, not guaranteed nor subject to production testing
- Guarantee by design, nor subjected to production test
- V_{IN} = input voltage to perform proper function
- Guaranteed by 5 V leakage testing, not production tested




TYPICAL CHARACTERISTICS (25 °C, unless otherwise noted)




$R_{DS(on)}$ vs. V_{COM} and Supply Voltage




$R_{DS(on)}$ vs. V_{COM} and Temperature




$R_{DS(on)}$ vs. V_{COM} and Temperature



Leakage Current vs. Temperature




$R_{DS(on)}$ vs. V_{COM} and Temperature




Leakage Current vs. Temperature




TYPICAL CHARACTERISTICS (25 °C, unless otherwise noted)




Leakage Current vs. Temperature




Insertion Loss, Off-Isolation Crosstalk vs. Frequency




Supply Current vs. Temperature








Supply Current vs. Input Switching Frequency




Supply Current vs. Temperature




Switching Time vs. Temperature and Supply Voltage





TYPICAL CHARACTERISTICS (25 °C, unless otherwise noted)

Switching Threshold vs. Supply Voltage

Supply Current vs. Enable Input Voltage

Charge Injection vs. Analog Voltage

Power Down Leakage Current vs. Temperature

Power Down Leakage Current vs. V_{COM}

TEST CIRCUITS

 C_L (includes fixture and stray capacitance)

$$V_{OUT} = V_{COM} \left(\frac{R_L}{R_L + R_{ON}} \right)$$





Logic "1" = Switch On
Logic input waveforms inverted for switches that have the opposite logic sense.

Fig. 1 - Switching Time

 C_L (includes fixture and stray capacitance)

Fig. 2 - Break-Before-Make Interval


IN depends on switch configuration: input polarity determined by sense of switch.

Fig. 3 - Charge Injection

TEST CIRCUITS

Fig. 4 - Off-Isolation

Fig. 5 - Channel Off / On Capacitance




PRODUCT SUMMARY	
Part number	DG2001E
Status code	2
Configuration	SPDT x 1
Single supply min. (V)	1.8
Single supply max. (V)	5.5
Dual supply min. (V)	-
Dual supply max. (V)	-
On-resistance (Ω)	0.85
Charge injection (pC)	8
Source on capacitance (pF)	53
Source off capacitance (pF)	16
Leakage switch on typ. (nA)	0.05
Leakage switch off max. (nA)	5
-3 dB bandwidth (MHz)	-
Package	TSOP-6
Functional circuit / applications	Multi purpose, instrumentation, medical and healthcare, portable
Interface	Binary
Single supply operation	Yes
Dual supply operation	-
Turn on time max. (ns)	32
Crosstalk and off isolation	-63


Vishay Siliconix maintains worldwide manufacturing capability. Products may be manufactured at one of several qualified locations. Reliability data for Silicon Technology and Package Reliability represent a composite of all qualified locations. For related documents such as package / tape drawings, part marking, and reliability data, see www.vishay.com/ppg?76471.

TSOP: 5/6-LEAD



JEDEC Part Number: MO-193C



5-LEAD TSOP




6-LEAD TSOP




	MILLIMETERS			INCHES		
Dim	Min	Nom	Max	Min	Nom	Max
A	0.91	-	1.10	0.036	-	0.043
A ₁	0.01	-	0.10	0.0004	-	0.004
A ₂	0.90	-	1.00	0.035	0.038	0.039
b	0.30	0.32	0.45	0.012	0.013	0.018
c	0.10	0.15	0.20	0.004	0.006	0.008
D	2.95	3.05	3.10	0.116	0.120	0.122
E	2.70	2.85	2.98	0.106	0.112	0.117
E ₁	1.55	1.65	1.70	0.061	0.065	0.067
e	0.95 BSC			0.0374 BSC		
e ₁	1.80	1.90	2.00	0.071	0.075	0.079
L	0.32	-	0.50	0.012	-	0.020
L ₁	0.60 Ref			0.024 Ref		
L ₂	0.25 BSC			0.010 BSC		
R	0.10	-	-	0.004	-	-
θ	0°	4°	8°	0°	4°	8°
θ ₁	7° Nom			7° Nom		
ECN: C-06593-Rev. I, 18-Dec-06						
DWG: 5540						


Recommended Land Pattern For TSOP-5L / TSOP-6L



TSOP 5L



TSOP 6L


Note

- All dimensions are in inches (millimeter)

ECN: C22-0860-Rev. B, 24-Oct-2022
DWG: 3010



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Vishay products are not designed for use in life-saving or life-sustaining applications or any application in which the failure of the Vishay product could result in personal injury or death unless specifically qualified in writing by Vishay. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.