


R-C Thermal Model Parameters

DESCRIPTION

The parametric values in the R-C thermal model have been derived using curve-fitting techniques. R-C values for the electrical circuit in the Foster/tank and Cauer/filter configurations are included. When implemented in PSpice, these values have matching characteristic curves to the single-pulse transient thermal impedance curves for the MOSFET.

These RC values can be used in the PSpice simulation to evaluate the thermal behavior of the MOSFET junction temperature under a defined power profile. These techniques are described in application note AN609, "Thermal Simulation of Power MOSFETs on the PSpice Platform".

R-C THERMAL MODEL FOR TANK CONFIGURATION



R-C VALUES FOR TANK CONFIGURATION			
THERMAL RESISTANCE (°C/W)			
Junction to	Ambient	Case	Foot
RT1	1.8464	1.4401	n/a
RT2	9.2164	599.8824m	n/a
RT3	16.8859	2.5349	n/a
RT4	57.0513	925.1176m	n/a
THERMAL CAPACITANCE (Joules/°C)			
Junction to	Ambient	Case	Foot
CT1	637.5899u	13.1661m	n/a
CT2	4.9698m	911.9265u	n/a
CT3	94.9162m	1.0314m	n/a
CT4	1.2862	328.5748m	n/a


Note

- n/a indicates not applicable

This document is intended as a SPICE modeling guideline and does not constitute a commercial product datasheet. Designers should refer to the appropriate datasheet of the same number for guaranteed specification limits.



R-C THERMAL MODEL FOR FILTER CONFIGURATION



R-C VALUES FOR FILTER CONFIGURATION			
THERMAL RESISTANCE (°C/W)			
Junction to	Ambient	Case	Foot
RF1	8.3333	1.4470	n/a
RF2	16.8338	1.9879	n/a
RF3	29.3127	1.2262	n/a
RF4	30.5202	838.8999m	n/a
THERMAL CAPACITANCE (Joules/°C)			
Junction to	Ambient	Case	Foot
CF1	1.4933m	406.7999u	n/a
CF2	39.8787m	711.8035u	n/a
CF3	740.3289m	12.1527m	n/a
CF4	1.4956	345.9767m	n/a

Note

- n/a indicates not applicable

