


## IR Receiver Modules for Remote Control Systems



### FEATURES

- Improved dark sensitivity
- Improved immunity against optical noise
- Very low supply current
- Photo detector and preamplifier in one package
- Internal filter for PCM frequency
- Supply voltage: 2.5 V to 3.6 V
- Material categorization:  
for definitions of compliance please see [www.vishay.com/doc?99912](http://www.vishay.com/doc?99912)



**RoHS**  
COMPLIANT  
HALOGEN  
**FREE**  
**GREEN**  
(5-2008)

### LINKS TO ADDITIONAL RESOURCES



### MECHANICAL DATA

1 = OUT, 2 = GND, 3 =  $V_S$

### ORDERING CODE

TSOP98... - 1500 pieces in bags

### DESCRIPTION


The TSOP98... series devices are the latest generation miniaturized IR receiver modules for infrared remote control systems. This series provides improvements in sensitivity to remote control signals in dark ambient as well as in sensitivity in the presence of optical disturbances e.g. from CFLs.

The devices contain a PIN diode and a preamplifier assembled on a lead frame. The epoxy package contains an IR filter. The demodulated output signal can be directly connected to a microprocessor for decoding.


The TSOP983.. and TSOP985.. series devices are designed to receive short burst codes (6 or more carrier cycles per burst). The third digit designates the AGC level (AGC3 or AGC5) and the last two digits designate the band-pass frequency (see table below). The higher the AGC, the better noise is suppressed, but the lower the code compatibility. AGC3 provides enhanced noise suppression and AGC5 provides maximized noise suppression. Generally, we advise to select the highest AGC that satisfactorily receives the desired remote code.

These components have not been qualified to automotive specifications.

### BLOCK DIAGRAM



### APPLICATION CIRCUIT



$R_1$  and  $C_1$  recommended to reduce supply ripple for  $V_S < 2.2$  V



| PARTS TABLE       |        |                                                                                                  |                                    |
|-------------------|--------|--------------------------------------------------------------------------------------------------|------------------------------------|
| AGC               |        | ENHANCED NOISE SUPPRESSION (AGC3)                                                                | MAXIMIZED NOISE SUPPRESSION (AGC5) |
| Carrier frequency | 30 kHz | TSOP98330                                                                                        | TSOP98530                          |
|                   | 33 kHz | TSOP98333                                                                                        | TSOP98533                          |
|                   | 36 kHz | TSOP98336 <sup>(1)</sup>                                                                         | TSOP98536                          |
|                   | 38 kHz | TSOP98338 <sup>(2)(4)</sup>                                                                      | TSOP98538                          |
|                   | 40 kHz | TSOP98340                                                                                        | TSOP98540                          |
|                   | 56 kHz | TSOP98356                                                                                        | TSOP98556 <sup>(3)</sup>           |
| Package           |        | Minicast                                                                                         |                                    |
| Pinning           |        | 1 = OUT, 2 = GND, 3 = V <sub>S</sub>                                                             |                                    |
| Dimensions (mm)   |        | 5.0 W x 6.95 H x 4.8 D                                                                           |                                    |
| Mounting          |        | Leaded                                                                                           |                                    |
| Application       |        | Remote control                                                                                   |                                    |
| Best choice for   |        | <sup>(1)</sup> RCMM <sup>(2)</sup> RECS-80 Code <sup>(3)</sup> r-map <sup>(4)</sup> XMP-1, XMP-2 |                                    |

**Note**

- 30 kHz and 33 kHz only available on written request

| ABSOLUTE MAXIMUM RATINGS    |                          |                  |                                |      |
|-----------------------------|--------------------------|------------------|--------------------------------|------|
| PARAMETER                   | TEST CONDITION           | SYMBOL           | VALUE                          | UNIT |
| Supply voltage              |                          | V <sub>S</sub>   | -0.3 to +3.6                   | V    |
| Supply current              |                          | I <sub>S</sub>   | 3                              | mA   |
| Output voltage              |                          | V <sub>O</sub>   | -0.3 to (V <sub>S</sub> + 0.3) | V    |
| Output current              |                          | I <sub>O</sub>   | 5                              | mA   |
| Junction temperature        |                          | T <sub>j</sub>   | 100                            | °C   |
| Storage temperature range   |                          | T <sub>stg</sub> | -25 to +85                     | °C   |
| Operating temperature range |                          | T <sub>amb</sub> | -25 to +85                     | °C   |
| Power consumption           | T <sub>amb</sub> ≤ 85 °C | P <sub>tot</sub> | 10                             | mW   |
| Soldering temperature       | t ≤ 10 s, 1 mm from case | T <sub>sd</sub>  | 260                            | °C   |

**Note**

- Stresses beyond those listed under “Absolute Maximum Ratings” may cause permanent damage to the device. This is a stress rating only and functional operation of the device at these or any other conditions beyond those indicated in the operational sections of this specification is not implied. Exposure to absolute maximum rating conditions for extended periods may affect the device reliability

| ELECTRICAL AND OPTICAL CHARACTERISTICS (T <sub>amb</sub> = 25 °C, unless otherwise specified) |                                                                                                                        |                     |      |      |      |                   |
|-----------------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------------------------------------|---------------------|------|------|------|-------------------|
| PARAMETER                                                                                     | TEST CONDITION                                                                                                         | SYMBOL              | MIN. | TYP. | MAX. | UNIT              |
| Supply current                                                                                | E <sub>v</sub> = 0, V <sub>S</sub> = 3.3 V                                                                             | I <sub>SD</sub>     | 0.25 | 0.37 | 0.45 | mA                |
|                                                                                               | E <sub>v</sub> = 40 klx, sunlight                                                                                      | I <sub>SH</sub>     | -    | 0.50 | -    | mA                |
| Supply voltage                                                                                |                                                                                                                        | V <sub>S</sub>      | 2.0  | -    | 3.6  | V                 |
| Transmission distance                                                                         | E <sub>v</sub> = 0, test signal see Fig. 1, IR diode TSAL6200, I <sub>F</sub> = 50 mA                                  | d                   | -    | 21   | -    | m                 |
| Output voltage low                                                                            | I <sub>OSL</sub> = 0.5 mA, E <sub>e</sub> = 0.7 mW/m <sup>2</sup> , test signal see Fig. 1                             | V <sub>OSL</sub>    | -    | -    | 100  | mV                |
| Minimum irradiance                                                                            | Test signal: XMP code                                                                                                  | E <sub>e min.</sub> | -    | 0.20 | 0.40 | mW/m <sup>2</sup> |
|                                                                                               | Test signal: NEC code                                                                                                  |                     | -    | 0.15 | 0.30 |                   |
| Maximum irradiance                                                                            | t <sub>pi</sub> - 3.0/f <sub>0</sub> < t <sub>po</sub> < t <sub>pi</sub> + 3.5/f <sub>0</sub> , test signal see Fig. 1 | E <sub>e max.</sub> | 30   | -    | -    | W/m <sup>2</sup>  |
| Directivity                                                                                   | Angle of half transmission distance                                                                                    | Φ <sub>1/2</sub>    | -    | ± 45 | -    | °                 |


**TYPICAL CHARACTERISTICS** ( $T_{amb} = 25\text{ }^{\circ}\text{C}$ , unless otherwise specified)


Fig. 1 - Output Delay and Pulse-Width




Fig. 4 - Pulse-Width vs. Irradiance in Dark Ambient




Fig. 2 - Pulse-Width vs. Irradiance in Dark Ambient




Fig. 5 - Frequency Dependence of Responsivity




Fig. 3 - Test Signal




Fig. 6 - Sensitivity in Bright Ambient




Fig. 7 - Sensitivity vs. Supply Voltage Disturbances




Fig. 9 - Sensitivity vs. Ambient Temperature




Fig. 8 - Max. Envelope Duty Cycle vs. Burst Length




Fig. 10 - Relative Spectral Sensitivity vs. Wavelength




Fig. 11 - Horizontal and Vertical Directivity




Fig. 12 - Sensitivity vs. Supply Voltage

## SUITABLE DATA FORMAT

This series is designed to suppress spurious output pulses due to noise or disturbance signals. The devices can distinguish data signals from noise due to differences in frequency, burst length, and envelope duty cycle. The data signal should be close to the device's band-pass center frequency (e.g. 38 kHz) and fulfill the conditions in the table below.

When a data signal is applied to the product in the presence of a disturbance, the sensitivity of the receiver is automatically reduced by the AGC to insure that no spurious pulses are present at the receiver's output.

Some examples which are suppressed are:

- DC light (e.g. from tungsten bulbs sunlight)
- Continuous signals at any frequency
- Strongly or weakly modulated patterns from fluorescent lamps with electronic ballasts (see Fig. 13 or Fig. 14)



Fig. 13 - IR Disturbance from Fluorescent Lamp With Low Modulation



Fig. 14 - IR Disturbance from Fluorescent Lamp With High Modulation


|                                                                               | TSOP983..                       | TSOP985..                    |
|-------------------------------------------------------------------------------|---------------------------------|------------------------------|
| Minimum burst length                                                          | 6 cycles/burst                  | 6 cycles/burst               |
| After each burst of length<br>A gap time is required of                       | 6 to 20 cycles<br>≥ 8 cycles    | 6 to 38 cycles<br>≥ 8 cycles |
| For bursts greater than<br>a minimum gap time in the data stream is needed of | 20 cycles<br>> 6 x burst length | 38 cycles<br>> 20 ms         |
| Maximum number of continuous short bursts/second                              | 2500                            | 2500                         |
| RCMM code                                                                     | Preferred                       | Yes                          |
| XMP-1 code                                                                    | Preferred                       | Yes                          |
| r-map code                                                                    | Yes                             | Preferred                    |
| RECS-80 code                                                                  | Preferred                       | Yes                          |
| Suppression of interference from fluorescent lamps                            | Fig. 13 and Fig. 14             | Fig. 13 and Fig. 14          |

### Note

- For data formats with long bursts (more than 10 carrier cycles) please see the datasheet for TSOP982.., TSOP984.., or TSOP986..



PACKAGE DIMENSIONS in millimeters





## Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Vishay products are not designed for use in life-saving or life-sustaining applications or any application in which the failure of the Vishay product could result in personal injury or death unless specifically qualified in writing by Vishay. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.