


Three Phase Bridge (Power Modules), 40 A



MTK

FEATURES

- Package fully compatible with the industry standard INT-A-PAK power modules series
- High thermal conductivity package, electrically insulated case
- Excellent power volume ratio, outline for easy connections to power transistor and IGBT modules
- 4000 V_{RMS} isolating voltage
- Designed and qualified for industrial level
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912


RoHS
COMPLIANT

PRIMARY CHARACTERISTICS

I _O	40 A
V _{RRM}	1600 V
Package	MTK
Circuit configuration	Three phase bridge

DESCRIPTION

A range of extremely compact, encapsulated three phase bridge rectifiers offering efficient and reliable operation. They are intended for use in general purpose and heavy duty applications.

MAJOR RATINGS AND CHARACTERISTICS

SYMBOL	CHARACTERISTICS	VALUES	UNITS
I _O		40 (50)	A
	T _C	85 (60)	°C
I _{FSM}	50 Hz	270	A
	60 Hz	280	
I ² _t	50 Hz	365	kA ² s
	60 Hz	325	
I ² _{√t}		3650	kA ² √s
V _{RRM}		1600	V
T _{Stg}	Range	-40 to +150	°C
T _J			

ELECTRICAL SPECIFICATIONS

VOLTAGE RATINGS

TYPE NUMBER	VOLTAGE CODE	V _{RRM} , MAXIMUM REPETITIVE PEAK REVERSE VOLTAGE V	V _{RSM} , MAXIMUM NON-REPETITIVE PEAK REVERSE VOLTAGE V	I _{RRM} MAXIMUM AT T _J MAXIMUM mA
40MT..K	160	1600	1700	10



FORWARD CONDUCTION						
PARAMETER	SYMBOL	TEST CONDITIONS			VALUES	UNITS
Maximum DC output current at case temperature	I _O	120° rect. conduction angle			40 (50)	A
					85 (60)	°C
Maximum peak, one-cycle forward, non-repetitive surge current	I _{FSM}	t = 10 ms	No voltage reapplied	Initial T _J = T _J maximum	270	A
		t = 8.3 ms			280	
		t = 10 ms	100 % V _{RRM} reapplied		225	
		t = 8.3 ms			240	
Maximum I ² t for fusing	I ² t	t = 10 ms	No voltage reapplied		365	kA ² s
		t = 8.3 ms			325	
		t = 10 ms	100 % V _{RRM} reapplied		253	
		t = 8.3 ms			240	
Maximum I ² √t for fusing	I ² √t	t = 0.1 ms to 10 ms, no voltage reapplied			3650	A ² √s
Low level value of threshold voltage	V _{F(TO)1}	(16.7 % x π x I _{F(AV)} < I < π x I _{F(AV)}), T _J maximum			0.78	V
High level value of threshold voltage	V _{F(TO)2}	(I > π x I _{F(AV)}), T _J maximum			0.9	
Low level value of forward slope resistance	r _{f1}	(16.7 % x π x I _{F(AV)} < I < π x I _{F(AV)}), T _J maximum			15	mΩ
High level value of forward slope resistance	r _{f2}	(I > π x I _{F(AV)}), T _J maximum			14.1	
Maximum forward voltage drop	V _{FM}	I _{pk} = 100 A, T _J = 25 °C, t _p = 400 μs single junction			2.02	V
RMS isolation voltage	V _{ISOL}	T _J = 25 °C, all terminal shorted f = 50 Hz, t = 1 s			4000	

THERMAL AND MECHANICAL SPECIFICATIONS					
PARAMETER		SYMBOL	TEST CONDITIONS	VALUES	UNITS
Maximum junction operating and storage temperature range		T _J , T _{Stg}		-40 to +150	°C
Maximum thermal resistance, junction to case		R _{thJC}	DC operation per module	0.41	K/W
			DC operation per junction	2.46	
			120° rect. conduction angle per module	0.45	
			120° rect. conduction angle per junction	2.7	
Maximum thermal resistance, case to heatsink per module		R _{thCS}	Mounting surface smooth, flat and greased	0.03	
Mounting torque ± 10 %		to heatsink to terminal	A mounting compound is recommended and the torque should be rechecked after a period of 3 hours to allow for the spread of the compound. Lubricated threads.	4 to 6	Nm
				3 to 4	
Approximate weight				176	g




Fig. 1 - Current Ratings Characteristics




Fig. 2 - Forward Voltage Drop Characteristics





Fig. 3 - Total Power Loss Characteristics




Fig. 4 - Maximum Non-Repetitive Surge Current





Fig. 5 - Maximum Non-Repetitive Surge Current


Fig. 6 - Thermal Impedance Z_{thJC} Characteristics


ORDERING INFORMATION TABLE

Device code	VS-	4	0	MT	160	K	PbF
	①	②	③	⑤	⑥		⑦
①	- Vishay Semiconductors product						
②	- Current rating code: 4 = 40 A (average)						
③	- Three phase diodes bridge						
④	- Essential part number						
⑤	- Voltage code x 10 = V_{RRM} (see Voltage Ratings table)						
⑥	- PbF = lead (Pb)-free						

Note

- To order the optional hardware go to www.vishay.com/doc?95172

CIRCUIT CONFIGURATION



LINKS TO RELATED DOCUMENTS	
Dimensions	www.vishay.com/doc?95004



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Vishay products are not designed for use in life-saving or life-sustaining applications or any application in which the failure of the Vishay product could result in personal injury or death unless specifically qualified in writing by Vishay. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.