


SMF (DO-219AB)

TAPE INFORMATION




DIMENSIONS in millimeters (inches)							
TAPE SIZE	D ₀	E ₁	P ₀	P ₂	S ₁ MIN.	T MAX.	T ₁ MAX.
8 (0.315)	1.5 + 0.1 / - 0.0 (0.059 + 0.004 / - 0.000)	1.75 ± 0.1 (0.069 ± 0.004)	4.0 ± 0.1 (0.157 ± 0.004)	2.0 ± 0.05 (0.079 ± 0.002)	0.6 (0.024)	0.6 (0.024)	0.1 (0.004)
B ₁ MAX.	D ₁ MIN.	E ₂ MIN.	F	P ₁	R REF.	T ₂ MAX.	W MAX.
4.35 (0.171)	1.0 (0.039)	6.25 (0.246)	3.5 ± 0.05 (0.138 ± 0.002)	4.0 ± 0.10 (0.157 ± 0.004)	20 (0.787)	1.8 (0.07)	8.2 (0.322)

Notes

- (1) For machine reference only, including draft and radii concentric around B₀
- (2) A₀, B₀, and K₀ are determined by the maximum dimensions of the component size. The clearance between the component and the cavity must be within 0.05 mm (0.002") min. to 0.5 mm (0.02") max. for 8 mm tape
- (3) All surface-mount components are packed in accordance with EIA standard 481-F

REEL INFORMATION



DIMENSIONS in millimeters (inches)							
PACKAGE CODE	A	B MIN.	C	D MIN.	N MIN.	G MAX.	T MAX.
I, 18 (13" Reel)	330 ± 2.0 (13.0 ± 0.079)	1.5 (0.059)	13.0 + 0.50 / - 0.20 (0.51 + 0.020 / - 0.008)	20.2 (0.795)	50 (1.97)	9.9 (0.389)	14.4 (0.567)
H, 08 (7" Reel)	178 ± 2.0 (7.0 ± 0.079)						