


Ultrafast Rectifier, 2 A FRED Pt®

eSMP® Series


SMP (DO-220AA)

Cathode  Anode

RoHS
COMPLIANT
HALOGEN
FREE

FEATURES

- Very low profile - typical height of 1.0 mm
- Ideal for automated placement
- Low forward voltage drop, low power losses
- Low leakage current
- Meets MSL level 1, per J-STD-020, LF maximum peak of 260 °C
- For PFC, CRM snubber operation
- AEC-Q101 qualified
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912

TYPICAL APPLICATIONS

For use in high frequency, freewheeling, DC/DC converters, PFC, and in snubber industrial and automotive applications.

MECHANICAL DATA

Case: SMP (DO-220AA)

Molding compound meets UL 94 V-0 flammability rating

Terminals: matte tin plated leads, solderable per J-STD-002, meets JESD 201 class 2 whisker test

Polarity: color band denotes cathode end

LINKS TO ADDITIONAL RESOURCES



PRIMARY CHARACTERISTICS	
$I_{F(AV)}$	2 A
V_R	100 V, 200 V
V_F at I_F	0.79 V
I_{FSM}	40 A
t_{rr} (typ.)	23 ns
T_J max.	175 °C
Package	SMP (DO-220AA)
Circuit configuration	Single

ABSOLUTE MAXIMUM RATINGS					
PARAMETER		SYMBOL	TEST CONDITIONS	VALUES	UNITS
Peak repetitive reverse voltage	VS-2ENH01HM3	V_{RRM}		100	V
	VS-2ENH02HM3			200	
Average rectified forward current		$I_{F(AV)}$	$T_C = 158\text{ °C}$	2	A
Non-repetitive peak surge current		I_{FSM}	$T_J = 25\text{ °C}$, 10 ms sine pulse	40	
Operating junction and storage temperatures		T_J, T_{Stg}		-55 to +175	°C

ELECTRICAL SPECIFICATIONS ($T_J = 25\text{ °C}$ unless otherwise specified)							
PARAMETER		SYMBOL	TEST CONDITIONS	MIN.	TYP.	MAX.	UNITS
Breakdown voltage, blocking voltage	VS-2ENH01HM3	V_{BR}, V_R	$I_R = 100\text{ }\mu\text{A}$	100	-	-	V
	VS-2ENH02HM3			200	-	-	
Forward voltage		V_F	$I_F = 2\text{ A}$	-	0.94	1.00	
			$I_F = 2\text{ A}, T_J = 150\text{ °C}$	-	0.79	0.84	
Reverse leakage current		I_R	$V_R = V_R$ rated	-	-	2	μA
			$T_J = 150\text{ °C}, V_R = V_R$ rated	-	-	20	
Junction capacitance		C_T	$V_R = 200\text{ V}$	-	8	-	pF



DYNAMIC RECOVERY CHARACTERISTICS ($T_J = 25\text{ }^{\circ}\text{C}$ unless otherwise specified)						
PARAMETER	SYMBOL	TEST CONDITIONS	MIN.	TYP.	MAX.	UNITS
Reverse recovery time	t_{rr}	$I_F = 1.0\text{ A}$, $di_F/dt = 100\text{ A}/\mu\text{s}$, $V_R = 30\text{ V}$	-	23	-	ns
		$I_F = 0.5\text{ A}$, $I_R = 1\text{ A}$, $I_{rr} = 0.25\text{ A}$	-	-	28	
		$T_J = 25\text{ }^{\circ}\text{C}$	-	16	-	
		$T_J = 125\text{ }^{\circ}\text{C}$	-	25	-	
Peak recovery current	I_{RRM}	$T_J = 25\text{ }^{\circ}\text{C}$	-	2.0	-	A
		$T_J = 125\text{ }^{\circ}\text{C}$	-	3.1	-	
Reverse recovery charge	Q_{rr}	$T_J = 25\text{ }^{\circ}\text{C}$	-	15	-	nC
		$T_J = 125\text{ }^{\circ}\text{C}$	-	37	-	

THERMAL - MECHANICAL SPECIFICATIONS						
PARAMETER	SYMBOL	TEST CONDITIONS	MIN.	TYP.	MAX.	UNITS
Maximum junction and storage temperature range	T_J, T_{Stg}		-55	-	175	$^{\circ}\text{C}$
Thermal resistance, junction to mount	$R_{thJM}^{(1)}$	Infinite heatsink	-	7	9	$^{\circ}\text{C}/\text{W}$
Thermal resistance, junction to ambient	R_{thJA}	PCB footprint 4.8 mm x 4.8 mm	-	107	-	
Approximate weight				0.024		g
Marking device	VS-2ENH01HM3	Case style SMP (DO-220AA)		2H1		
	VS-2ENH02HM3			2H2		

Note

(1) Thermal resistance junction to mount follows JEDEC® 51-14 transient dual interface test method (TDIM)




Fig. 1 - Typical Forward Voltage Drop Characteristics




Fig. 2 - Typical Values of Reverse Current vs. Reverse Voltage




Fig. 3 - Typical Junction Capacitance vs. Reverse Voltage




Fig. 4 - Transient Thermal Impedance, Junction to Case




Fig. 5 - Maximum Allowable Case Temperature vs. Average Forward Current






Fig. 6 - Forward Power Loss Characteristics


Fig. 7 - Typical Reverse Recovery Time vs. dI_F/dt

Fig. 8 - Typical Stored Charge vs. dI_F/dt
Note

- (1) Formula used: $T_C = T_J - (P_d + P_{dREV}) \times R_{thJC}$;
 P_d = forward power loss = $I_{F(AV)} \times V_{FM}$ at $(I_{F(AV)}/D)$ (see fig. 5);
 P_{dREV} = inverse power loss = $V_{R1} \times I_R (1 - D)$; I_R at V_{R1} = rated V_R




Fig. 9 - Reverse Recovery Waveform and Definitions

**ORDERING INFORMATION TABLE**

Device code	VS-	2	E	N	H	02	H	M3
	1	2	3	4	5	6	7	8
	1	-	Vishay Semiconductors product					
	2	-	Current rating (2 = 2 A)					
	3	-	Circuit configuration: E = single diode					
	4	-	N = SMP package					
	5	-	Process type, H = ultrafast recovery					
	6	-	Voltage code (02 = 200 V)					
	7	-	H = AEC-Q101 qualified					
	8	-	M3 = halogen-free, RoHS-compliant, and terminations lead (Pb)-free					


ORDERING INFORMATION (Example)			
PREFERRED P/N	PREFERRED PACKAGE CODE	MINIMUM ORDER QUANTITY	PACKAGING DESCRIPTION
VS-2ENH01HM3/84A	84A	3000	7" diameter plastic tape and reel
VS-2ENH01HM3/85A	85A	10 000	13" diameter plastic tape and reel
VS-2ENH02HM3/84A	84A	3000	7" diameter plastic tape and reel
VS-2ENH02HM3/85A	85A	10 000	13" diameter plastic tape and reel

LINKS TO RELATED DOCUMENTS	
Dimensions	www.vishay.com/doc?96547
Part marking information	www.vishay.com/doc?96574
Packaging information	www.vishay.com/doc?88869
SPICE model	www.vishay.com/doc?96551




SMP (DO-220AA)

DIMENSIONS in inches (millimeters)



Mounting pad layout:





Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Vishay products are not designed for use in life-saving or life-sustaining applications or any application in which the failure of the Vishay product could result in personal injury or death unless specifically qualified in writing by Vishay. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.