

Insulated Gen 2 Schottky Rectifier Module, 200 A



SOT-227

LINKS TO ADDITIONAL RESOURCES



PRIMARY CHARACTERISTICS	
$I_{F(AV)}$ per module at $T_C = 82\text{ }^{\circ}\text{C}$	200 A
V_R	100 V
V_{FM} at 100 A, $T_C = 25\text{ }^{\circ}\text{C}$	0.83 V
Package	SOT-227
Circuit configuration	Two separate diodes, parallel pin-out

FEATURES

- Max. $T_J = 150\text{ }^{\circ}\text{C}$
- Two fully independent diodes
- Fully insulated package
- Trench MOS Barrier Schottky technology
- Ultra low forward voltage drop
- Optimized for power conversion: welding and industrial SMPS applications
- Easy to use and parallel
- Industry standard outline
- Designed and qualified for industrial level
- UL approved file E78996 
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912


RoHS
COMPLIANT

DESCRIPTION

The VS-QA200FA10 insulated modules integrate two state of the art Trench MOS Schottky technology rectifiers in the compact, industry standard SOT-227 package.

These devices are thus intended for high frequency converters and switching power supplies.

MAJOR RATINGS AND CHARACTERISTICS			
SYMBOL	CHARACTERISTICS	VALUES	UNITS
V_F	$I_F = 100\text{ A}$, $T_J = 150\text{ }^{\circ}\text{C}$	0.67	V
T_J	Range	-40 to +150	$^{\circ}\text{C}$

ABSOLUTE MAXIMUM RATINGS ($T_C = 25\text{ }^{\circ}\text{C}$ unless otherwise specified)				
PARAMETER	SYMBOL	TEST CONDITIONS	VALUES	UNITS
Cathode to anode voltage	V_R		100	V
Average forward current	$I_{F(AV)}$	$T_C = 82\text{ }^{\circ}\text{C}$	200	A
		$T_C = 82\text{ }^{\circ}\text{C}$	100	
Continuous forward current	I_F	$T_C = 90\text{ }^{\circ}\text{C}$	238	
		$T_C = 90\text{ }^{\circ}\text{C}$	119	
Single pulse forward current per diode	I_{FSM}	$T_C = 150\text{ }^{\circ}\text{C}$, $t = 6\text{ ms}$, square	765	
Maximum power dissipation per diode	P_D	$T_C = 90\text{ }^{\circ}\text{C}$	115	W
Non-repetitive avalanche energy per diode	E_{AS}	$T_J = 25\text{ }^{\circ}\text{C}$, $L = 1\text{ mH}$	1312	mJ
RMS isolation voltage	V_{ISOL}	Any terminal to case, $t = 1\text{ min}$	2500	V
Operating junction and storage temperatures	T_J , T_{Stg}		-40 to +150	$^{\circ}\text{C}$

ELECTRICAL SPECIFICATIONS PER DIODE ($T_J = 25\text{ }^{\circ}\text{C}$ unless otherwise specified)						
PARAMETER	SYMBOL	TEST CONDITIONS	MIN.	TYP.	MAX.	UNITS
Cathode to anode breakdown voltage	V_{BR}	$I_R = 2\text{ mA}$	100	-	-	V
Forward voltage	V_{FM}	$I_F = 100\text{ A}$	-	0.83	1.03	
		$I_F = 100\text{ A}$, $T_J = 150\text{ }^{\circ}\text{C}$	-	0.67	-	
Reverse leakage current	I_{RM}	$V_R = 100\text{ V}$	-	0.07	1.6	mA
		$T_J = 125\text{ }^{\circ}\text{C}$, $V_R = 100\text{ V}$	-	37	-	
Junction capacitance	C_T	$V_R = 100\text{ V}$, $f = 1\text{ MHz}$	-	514	-	pF



THERMAL - MECHANICAL SPECIFICATIONS						
PARAMETER	SYMBOL	TEST CONDITIONS	MIN.	TYP.	MAX.	UNITS
Junction-to-case, single leg conducting	R_{thJC}		-	-	0.52	$^{\circ}\text{C/W}$
Junction-to-case, both leg conducting			-	-	0.26	
Case-to-heatsink	R_{thCS}	Flat, greased surface	-	0.1	-	
Weight			-	30	-	g
Mounting torque		Torque to terminal	-	-	1.1 (9.7)	Nm (lbf.in)
		Torque to heatsink	-	-	1.8 (15.9)	Nm (lbf.in)
Case style			SOT-227			




Fig. 1 - Typical Forward Voltage Drop Characteristics




Fig. 3 - Typical Junction Capacitance vs. Reverse Voltage




Fig. 2 - Typical Values of Reverse Current vs. Reverse Voltage




Fig. 4 - Current Rating Characteristics





Fig. 5 - Total Power Loss Characteristics


Fig. 6 - Maximum Thermal Impedance Z_{thJC} Characteristics


ORDERING INFORMATION TABLE

Device code	VS-	Q	A	200	F	A	10
	①	②	③	④	⑤	⑥	⑦

- 1** - Vishay Semiconductors product
- 2** - Schottky technologies
- 3** - Present silicon generation
- 4** - Current rating (200 = 200 A)
- 5** - Circuit configuration (two separate diodes, parallel pin-out)
- 6** - Package indicator (SOT-227 standard insulated base)
- 7** - Voltage rating (10 = 100 V)

Quantity per tube is 10, M4 screw and washer included



CIRCUIT CONFIGURATION		
CIRCUIT	CIRCUIT CONFIGURATION CODE	CIRCUIT DRAWING
Two separate diodes, parallel pin-out	F	

LINKS TO RELATED DOCUMENTS	
Dimensions	www.vishay.com/doc?95423
Part marking information	www.vishay.com/doc?95425



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Vishay products are not designed for use in life-saving or life-sustaining applications or any application in which the failure of the Vishay product could result in personal injury or death unless specifically qualified in writing by Vishay. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.