


650 V Gen 3 Power SiC Merged PIN Schottky Diode, 2 A

eSMP® Series



Top View

Bottom View

SlimSMA HV (DO-221AC)

Cathode  Anode

LINKS TO ADDITIONAL RESOURCES



3D Models

PRIMARY CHARACTERISTICS	
$I_F^{(2)}$	2 A
V_R	650 V
V_F at I_F at 25 °C, typ.	1.30 V
T_J max.	175 °C
I_R at V_R at 175 °C	2.0 μ A
Q_C ($V_R = 400$ V)	7.2 nC
Package	SlimSMA HV (DO-221AC)
Circuit configuration	Single

FEATURES

- Minimum creepage distance 3.2 mm guaranteed by design
- Comparative Tracking Index: CTI ≥ 600
- High CTI molding compound provides excellent electrical insulation at relevant working voltages
- Positive V_F temperature coefficient for easy paralleling
- Virtually no recovery tail and no switching losses
- Temperature invariant switching behavior
- 175 °C maximum operating junction temperature
- Meets MSL level 1, per J-STD-020, LF maximum peak of 260 °C
- MPS structure for high ruggedness to forward current surge events
- Meets JESD 201 class 2 whisker test
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912


RoHS
COMPLIANT
HALOGEN
FREE

DESCRIPTION / APPLICATIONS

Wide band gap SiC based 650 V Schottky diode, designed for high performance and ruggedness.

Optimized for extreme high-speed hard switching over a wide temperature range. It is suited for demanding applications, such as bootstrap and anti-parallel diodes in AC/DC and DC/DC converters.

MECHANICAL DATA

Case: SlimSMA HV (DO-221AC)

Molding compound meets UL 94 V-0 flammability rating
Base P/N-M3 - halogen-free, RoHS-compliant

Terminals: matte tin plated leads, solderable per J-STD-002

MAXIMUM RATINGS ($T_A = 25$ °C unless otherwise specified)				
PARAMETER	SYMBOL	TEST CONDITIONS	VALUES	UNITS
Peak repetitive reverse voltage	V_{RRM}		650	V
Continuous forward current	I_F	$T_M = 140$ °C (DC) ⁽¹⁾	2	A
DC blocking voltage	V_{DC}		650	V
Repetitive peak forward current	I_{FRM}	$T_M = 25$ °C, $f = 50$ Hz, square wave, DC = 25 %	8	A
Non-repetitive peak forward surge current	I_{FSM}	$T_M = 25$ °C, $t_p = 10$ ms, half sine wave	16.5	
		$T_M = 110$ °C, $t_p = 10$ ms, half sine wave	14	
Power dissipation	$P_{tot}^{(1)}$	$T_M = 25$ °C	12.5	W
		$T_M = 110$ °C	5.4	
	$P_{tot}^{(2)}$	$T_M = 25$ °C	9.7	W
		$T_M = 110$ °C	4.2	
i^2t value	$\int i^2 dt$	$T_M = 25$ °C	1.4	A ² s
		$T_M = 110$ °C	1.0	
Operating junction and storage temperatures	$T_J^{(3)}, T_{Stg}$		-55 to +175	°C

Notes

⁽¹⁾ Based on typical R_{th}
⁽²⁾ Based on maximum R_{th}
⁽³⁾ The heat generated must be less than the thermal conductivity from junction-to-ambient: $dP_D/dT_J < 1/R_{\theta JA}$

ELECTRICAL SPECIFICATIONS ($T_J = 25\text{ }^{\circ}\text{C}$ unless otherwise specified)						
PARAMETER	SYMBOL	TEST CONDITIONS	MIN.	TYP.	MAX.	UNITS
Forward voltage	V_F	$I_F = 2\text{ A}$	-	1.30	1.50	V
		$I_F = 2\text{ A}, T_J = 150\text{ }^{\circ}\text{C}$	-	1.45	1.70	
		$I_F = 2\text{ A}, T_J = 175\text{ }^{\circ}\text{C}$	-	1.50	-	
Reverse leakage current	I_R	$V_R = V_R\text{ rated}$	-	0.1	15	μA
		$V_R = V_R\text{ rated}, T_J = 150\text{ }^{\circ}\text{C}$	-	0.5	30	
		$V_R = V_R\text{ rated}, T_J = 175\text{ }^{\circ}\text{C}$	-	2.0	-	
Total capacitance	C	$V_R = 1\text{ V}, f = 1\text{ MHz}$	-	100	-	pF
		$V_R = 400\text{ V}, f = 1\text{ MHz}$	-	12.5	-	
Total capacitive charge	Q_C	$V_R = 400\text{ V}, f = 1\text{ MHz}$	-	7.2	-	nC

THERMAL - MECHANICAL SPECIFICATIONS ($T_A = 25\text{ }^{\circ}\text{C}$ unless otherwise specified)						
PARAMETER	SYMBOL	TEST CONDITIONS	MIN.	TYP.	MAX.	UNITS
Thermal resistance, junction to mount	$R_{thJM}^{(1)}$		-	12	15.5	$^{\circ}\text{C/W}$
Marking device				C207		

Note

(1) Thermal resistance junction-to-mount follows JEDEC® 51-14 transient dual interface test method (TDIM)




Fig. 1 - Typical Forward Voltage Drop Characteristics




Fig. 3 - Typical Junction Capacitance vs. Reverse Voltage




Fig. 2 - Typical Values of Reverse Current vs. Reverse Voltage




Fig. 4 - Non-Repetitive Peak Forward Surge Current vs. Pulse Duration (Square Wave)




Fig. 5 - Typical Thermal Impedance Z_{thJM} Characteristics




Fig. 6 - Peak Forward Current vs. Maximum Allowable Mount Temperature




Fig. 8 - Typical Capacitive Energy vs. Reverse Voltage




Fig. 7 - Forward Power Loss Characteristics




Fig. 9 - Typical Capacitive Charge vs. Reverse Voltage

**ORDERING INFORMATION TABLE**

Device code	VS-	3C	02	E	J	07	-M3
	1	2	3	4	5	6	7
1	- Vishay Semiconductors product						
2	- 3C = SiC diode, generation 3						
3	- Current rating (02 = 2 A)						
4	- E = single diode						
5	- J = SlimSMA HV package						
6	- Voltage rating: (07 = 650 V)						
7	- Environmental digit: -M3 = halogen-free, RoHS-compliant, and termination lead (Pb)-free						

ORDERING INFORMATION

PREFERRED P/N	UNIT WEIGHT (g)	BASE QUANTITY	PACKAGING DESCRIPTION
VS-3C02EJ07-M3/H	0.032	3500 per reel	7" diameter plastic tape and reel
VS-3C02EJ07-M3/I	0.032	14 000 per reel	13" diameter plastic tape and reel


LINKS TO RELATED DOCUMENTS

Dimensions	www.vishay.com/doc?97278
Part marking information	www.vishay.com/doc?98699
Packaging information	www.vishay.com/doc?98714
SPICE model	www.vishay.com/doc?97542



SlimSMA HV (DO-221AC)

DIMENSIONS in inches (millimeters)



Notes

- (1) Minimum creepage distance is defined and guaranteed by design
- (2) For high voltage applications, end users should consider the relevant guidelines and normative on creepage and clearance distances between device terminals and PCB pads.



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Vishay products are not designed for use in life-saving or life-sustaining applications or any application in which the failure of the Vishay product could result in personal injury or death unless specifically qualified in writing by Vishay. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.