


Surface-Mount TRANSZORB® Transient Voltage Suppressors

eSMP® Series SMPD (TO-263AC)



RoHS
COMPLIANT
HALOGEN
FREE

FEATURES

- Junction passivation optimized design passivated anisotropic rectifier technology
- Unidirectional
- 7000 W peak pulse power capability with a 10/1000 μ s waveform (6600 W above 45 V)
- Low leakage current
- Low forward voltage drop
- High surge capability
- Meets MSL level 1, per J-STD-020, LF maximum peak of 260 °C
- Material categorization: for definitions of compliance please see www.vishay.com/doc?999912

TYPICAL APPLICATIONS

Use in sensitive electronics protection against voltage transients induced by inductive load switching and lightning, especially for ICs, MOSFET, signal lines of sensor units for consumer, computer, industrial, medical, and telecommunication.

LINKS TO ADDITIONAL RESOURCES



PRIMARY CHARACTERISTICS

V_{WM}	10 V to 70 V
V_{BR}	11.1 V to 86.0 V
P_{PPM} (10 x 1000 μ s)	7000 W, 6600 W
P_D	2.7 W
I_{FSM}	600 A
T_J max.	175 °C
Polarity	Unidirectional
Package	SMPD (TO-263AC)

MECHANICAL DATA

Case: SMPD (TO-263AC)

Molding compound meets UL 94 V-0 flammability rating

Base P/N-M3 - RoHS-compliant and industrial grade

Terminals: matte tin plated leads, solderable per J-STD-002 and JESD 22-B102

HM3 suffix meets JESD 201 class 2 whisker test

Polarity: heatsink is cathode

MAXIMUM RATINGS ($T_A = 25$ °C unless otherwise noted)

PARAMETER	SYMBOL	VALUE	UNIT
Peak pulse power dissipation with 10/1000 μ s waveform	P_{PPM}	7000, 6600	W
with 10/10 000 μ s waveform		2200, 1500	
Power dissipation on infinite heatsink at $T_A = 25$ °C	P_D	2.7	W
Peak pulse current with 10/1000 μ s waveform	$I_{PPM}^{(1)}$	See next table	A
Peak forward surge current 8.3 ms single half sine-wave	I_{FSM}	600	A
Operating junction and storage temperature range	T_J, T_{STG}	-55 to +175	°C

Note

⁽¹⁾ Non-repetitive current pulse at $T_A = 25$ °C

**ELECTRICAL CHARACTERISTICS** ($T_C = 25\text{ }^{\circ}\text{C}$ unless otherwise noted)

DEVICE TYPE	DEVICE MARKING CODE	BREAKDOWN VOLTAGE V_{BR} (V)			TEST CURRENT I_T (mA)	STAND-OFF VOLTAGE V_{WM} (V)	MAXIMUM REVERSE LEAKAGE AT V_{WM} I_R (μA)	MAXIMUM REVERSE LEAKAGE AT V_{WM} $T_J = 175\text{ }^{\circ}\text{C}$ I_R (μA)	MAX. PEAK PULSE CURRENT AT 10/1000 μs WAVEFORM I_{PPM} (A)	MAXIMUM CLAMPING VOLTAGE AT I_{PPM} V_C (V)	TYPICAL TEMP. COEFFICIENT OF V_{BR} α_T ($\%/^{\circ}\text{C}$)
		MIN.	NOM.	MAX.							
7KPD10A	7KPD10A	11.1	11.7	12.3	5.0	10.0	10	250	412	17.0	0.069
7KPD11A	7KPD11A	12.2	12.9	13.5	5.0	11.0	10	150	385	18.2	0.072
7KPD12A	7KPD12A	13.3	14.0	14.7	5.0	12.0	10	150	352	19.9	0.074
7KPD13A	7KPD13A	14.4	15.2	15.9	5.0	13.0	5	150	326	21.5	0.076
7KPD14A	7KPD14A	15.6	16.4	17.2	5.0	14.0	5	150	302	23.2	0.078
7KPD15A	7KPD15A	16.7	17.6	18.5	5.0	15.0	5	150	287	24.4	0.080
7KPD16A	7KPD16A	17.8	18.8	19.7	5.0	16.0	5	150	269	26.0	0.081
7KPD17A	7KPD17A	18.9	19.9	20.9	5.0	17.0	5	150	254	27.6	0.082
7KPD18A	7KPD18A	20.0	21.1	22.1	5.0	18.0	5	150	240	29.2	0.083
7KPD20A	7KPD20A	22.2	23.4	24.5	5.0	20.0	5	150	216	32.4	0.085
7KPD22A	7KPD22A	24.4	25.7	26.9	5.0	22.0	5	150	197	35.5	0.086
7KPD24A	7KPD24A	26.7	28.1	29.5	5.0	24.0	5	150	180	38.9	0.087
7KPD26A	7KPD26A	28.9	30.4	31.9	5.0	26.0	5	150	166	42.1	0.088
7KPD28A	7KPD28A	31.1	32.8	34.4	5.0	28.0	5	150	154	45.4	0.089
7KPD30A	7KPD30A	33.3	35.1	36.8	5.0	30.0	5	150	145	48.4	0.090
7KPD33A	7KPD33A	36.7	38.7	40.6	5.0	33.0	5	150	131	53.3	0.091
7KPD36A	7KPD36A	40.0	42.1	44.2	5.0	36.0	5	150	120	58.1	0.091
7KPD40A	7KPD40A	44.4	46.8	49.1	5.0	40.0	5	150	109	64.5	0.092
7KPD43A	7KPD43A	47.8	50.3	52.8	5.0	43.0	5	150	101	69.4	0.093
7KPD45A	7KPD45A	50.0	52.7	55.3	5.0	45.0	5	150	90.8	72.7	0.093
7KPD48A	7KPD48A	53.3	56.1	58.9	5.0	48.0	5	150	85.3	77.4	0.093
7KPD51A	7KPD51A	56.7	59.7	62.7	5.0	51.0	5	150	80.1	82.4	0.093
7KPD54A	7KPD54A	60.0	63.2	66.3	5.0	54.0	5	150	75.8	87.1	0.093
7KPD58A	7KPD58A	64.4	67.8	71.2	5.0	58.0	5	150	70.5	93.6	0.093
7KPD60A	7KPD60A	66.7	70.2	73.7	5.0	60.0	5	150	68.2	96.8	0.093
7KPD64A	7KPD64A	71.1	74.9	78.6	5.0	64.0	5	150	64.1	103	0.093
7KPD70A	7KPD70A	77.8	81.9	86.0	5.0	70.0	5	150	58.4	113	0.093

Notes

- For all types maximum $V_F = 1.9\text{ V}$ at $I_F = 100\text{ A}$ measured on $300\text{ }\mu\text{s}$ square pulse width
- (1) To calculate V_{BR} vs. junction temperature, use the following formula: V_{BR} at $T_J = V_{BR}$ at $25\text{ }^{\circ}\text{C} \times (1 + \alpha_T \times (T_J - 25))$

THERMAL CHARACTERISTICS ($T_A = 25\text{ }^{\circ}\text{C}$ unless otherwise noted)

PARAMETER	SYMBOL	VALUE	UNIT
Typical thermal resistance	$R_{\theta JA}$ (1)	55	$^{\circ}\text{C/W}$
	$R_{\theta JM}$ (2)	1.1	$^{\circ}\text{C/W}$

Notes

- (1) Thermal resistance junction-to-ambient to follow JEDEC®51-2A, device mounted on FR4 PCB, 2 oz. standard footprint
- (2) Thermal resistance junction-to-mount to follow JEDEC®51-14 using Transient Dual Interface Test Method (TDIM)

IMMUNITY TO STATIC ELECTRICAL DISCHARGE TO THE FOLLOWING STANDARDS($T_A = 25\text{ }^{\circ}\text{C}$ unless otherwise noted)

STANDARD	TEST TYPE	TEST CONDITIONS	SYMBOL	VALUE
IEC 61000-4-2	Contact discharge	$C = 150\text{ pF}$, $R = 330\text{ }\Omega$	ESD	30 kV
	Air discharge			30 kV



ORDERING INFORMATION TABLE

Device code

7K	PD	xxx	A	-	M3
①	②	③	④	⑤	⑥

- 1** - Peak pulse power rating (7K = 7000 W)
- 2** - Package type (PD = SMPD package)
- 3** - Stand-off voltage
- 4** - Breakdown voltage tolerance and polarity (A $\pm$ 5 %, unidirectional)
- 5** - Quality grade (H = AEC-Q101 qualified, otherwise = industry grade)
- 6** - Material / environment category (M3 = halogen-free, RoHS-compliant, and termination lead (Pb)-free)

ORDERING INFORMATION (Example)				
PREFERRED P/N	UNIT WEIGHT (g)	PREFERRED PACKAGE CODE	BASE QUANTITY	DELIVERY MODE
7KPD10A-M3/I	0.645	I	2000	13" diameter plastic tape and reel, anode towards the sprocket hole



RATINGS AND CHARACTERISTICS CURVES ($T_A = 25^\circ\text{C}$ unless otherwise noted)




Fig. 1 - Peak Pulse Power Derating Curve




Fig. 4 - Pulse Waveform




Fig. 2 - Power Derating Curve




Fig. 5 - Pulse Waveform




Fig. 3 - Typical Junction Capacitance





Fig. 6 - Typical Transient Thermal Impedance




PACKAGE OUTLINE DIMENSIONS in inches (millimeters)

SMPD (TO-263AC)



Mounting Pad Layout





Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Vishay products are not designed for use in life-saving or life-sustaining applications or any application in which the failure of the Vishay product could result in personal injury or death unless specifically qualified in writing by Vishay. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.