


Surface Mount XClampR® Transient Voltage Suppressors

High Temperature Stability and High Reliability Conditions



DO-218 Compatible



LINKS TO ADDITIONAL RESOURCES



PRIMARY CHARACTERISTICS	
V_{WM}	33 V to 85 V
V_{BR}	36.7 V to 104 V
P_{PPM} (10/1000 μ s)	11 000 W ⁽¹⁾
T_J max.	175 °C
Polarity	Bidirectional
Package	DO-218AC

Note

⁽¹⁾ Equivalent I_{PPM} with conventional 11 kW TVS

TYPICAL APPLICATIONS

Use in sensitive electronics protection against voltage transients induced by inductive load switching and lightning, especially for automotive load dump protection application.

FEATURES

- XClampR® flat clamping voltage
- Superior 8/20 μ s surge capability with low dynamic resistance
- $T_J = 175$ °C capability suitable for high reliability and automotive requirement
- Stable clamping voltage and breakdown voltage over wide temperature range
- Bidirectional
- Low leakage current
- AEC-Q101 qualified
 - Automotive ordering code: base P/NHM3
- Meets MSL level 1, per J-STD-020, LF maximum peak of 245 °C
- Material categorization: for definitions of compliance please see www.vishay.com/doc?999912



RoHS
COMPLIANT
HALOGEN
FREE

MECHANICAL DATA

Case: DO-218AC

Molding compound meets UL 94 V-0 flammability rating

Base P/NHM3 - halogen-free, RoHS-compliant, and AEC-Q101 qualified

Base P/N-M3 - halogen-free, RoHS-compliant, commercial grade

Terminals: matte tin plated leads, solderable per J-STD-002 and JESD 22-B102

HM3 suffix meet JESD 201 class 2 whisker test

Polarity: no cathode marking on bidirectional types

MAXIMUM RATINGS ($T_A = 25$ °C unless otherwise noted)			
PARAMETER	SYMBOL	VALUE	UNIT
Peak pulse power dissipation with 10/1000 μ s waveform	P_{PPM}	11 000 ⁽¹⁾	W
Peak pulse current with a 10/1000 μ s waveform	I_{PPM} ⁽²⁾	See next table	A
Operating junction and storage temperature range	T_J, T_{STG}	-55 to +175	°C

Notes

⁽¹⁾ The peak pulse power at equivalent I_{PPM} with conventional TVS

⁽²⁾ Non-repetitive current pulse and derated above $T_A = 25$ °C

**ELECTRICAL CHARACTERISTICS** ($T_A = 25\text{ }^{\circ}\text{C}$ unless otherwise noted)

DEVICE TYPE	BREAKDOWN VOLTAGE V_{BR} (V)			TEST CURRENT I_T (mA)	STAND-OFF VOLTAGE V_{WM} (V)	MAXIMUM REVERSE LEAKAGE AT V_{WM} I_R (μA)	MAXIMUM REVERSE LEAKAGE AT V_{WM} $T_J = 175\text{ }^{\circ}\text{C}$ I_R (μA)	CLAMPING VOLTAGE V_C AT I_{PPM} 10/1000 μs WAVEFORM			MAXIMUM CLAMPING VOLTAGE V_C AT I_{PPM} 8/20 μs WAVEFORM	
	MIN.	NOM.	MAX.					I_{PPM} (A)	V_C MIN.	V_C MAX.	I_{PPM} (A)	V_C
XFD11K33CA	36.7	38.7	40.6	5.0	33.0	10	150	207.1	33.8	40.6	2140	65.4
XFD11K36CA	40.0	42.1	44.2	5.0	36.0	10	150	190.4	36.8	44.2	2035	68.8
XFD11K40CA	44.4	46.8	49.1	5.0	40.0	10	150	170.3	40.9	49.1	1910	73.3
XFD11K43CA	47.8	50.3	52.8	5.0	43.0	10	150	158.8	43.9	52.8	1826	76.7
XFD11K45CA	50.0	52.7	55.3	5.0	45.0	10	150	151.6	46.0	55.3	1773	78.9
XFD11K48CA	53.3	56.1	58.9	5.0	48.0	10	150	142.5	49.0	58.9	1701	82.3
XFD11K51CA	56.7	59.7	62.7	5.0	51.0	10	150	133.8	52.2	62.7	1634	85.7
XFD11K54CA	60.0	63.2	66.3	5.0	54.0	10	150	126.6	55.2	66.3	1572	89.1
XFD11K58CA	64.4	67.8	71.2	5.0	58.0	10	150	117.7	59.2	71.2	1496	93.6
XFD11K60CA	66.7	70.2	73.7	5.0	60.0	10	150	113.9	61.3	73.7	1461	95.8
XFD11K64CA	71.1	74.9	78.6	5.0	64.0	10	150	107.0	65.4	78.6	1395	100.3
XFD11K70CA	77.8	81.9	86.0	5.0	70.0	10	150	97.5	71.5	86.0	1027	107.1
XFD11K75CA	83.3	87.7	92.1	5.0	75.0	10	150	91.0	76.6	92.1	976	112.7
XFD11K78CA	86.7	91.3	95.8	5.0	78.0	10	150	87.5	79.8	95.8	947	116.1
XFD11K85CA	94.4	99.2	104	5.0	85.0	10	150	80.5	86.7	104.0	887	124.0

THERMAL CHARACTERISTICS ($T_A = 25\text{ }^{\circ}\text{C}$ unless otherwise noted)

PARAMETER	SYMBOL	TYP.	UNIT
Thermal resistance	$R_{\theta JA}$ ⁽¹⁾	55	$^{\circ}\text{C/W}$
	$R_{\theta JM}$ ⁽²⁾	0.35	

Notes

⁽¹⁾ Thermal resistance junction-to-ambient to follow JEDEC[®] 51-2A, device mounted on FR4 PCB, 2 oz. standard footprint

⁽²⁾ Thermal resistance junction-to-mount to follow JEDEC[®] 51-14, using Transient Dual Interface Test Method (TDIM)

ORDERING INFORMATION TABLE

Device code	X	F	D	11K	xx	CA	H	M3
	①	②	③	④	⑤	⑥	⑦	⑧
①	- Vishay XClampR [®] TVS product							
②	- Flat clamping							
③	- Package type (D = SMD package)							
④	- Peak pulse power rating (11K = Equivalent I_{PPM} with conventional 11 kW)							
⑤	- Stand-off voltage							
⑥	- Breakdown voltage tolerance and polarity (CA $\pm 5\%$, bidirectional)							
⑦	- Quality grade (H = AEC-Q101 qualified, otherwise = industry grade)							
⑧	- Material / Environment category (M3 = halogen-free, RoHS-compliant, and termination lead (Pb)-free)							


ORDERING INFORMATION (Example)

PREFERRED P/N	UNIT WEIGHT (g)	PREFERRED PACKAGE CODE	BASE QUANTITY	DELIVERY MODE
XFD11K33CAHM3/I ⁽¹⁾	2.750	I	750	13" diameter plastic tape and reel
XFD11K33CA-M3/I	2.750	I	750	13" diameter plastic tape and reel

Note

⁽¹⁾ AEC-Q101 qualified

I - V CURVE CHARACTERISTICS



RATINGS AND CHARACTERISTICS CURVES ($T_A = 25^\circ\text{C}$ unless otherwise noted)




Fig. 1 - Peak Pulse Power Derating Curve





Fig. 3 - 10/1000 μs Pulse Waveform


Fig. 2 - Peak Pulse Current vs. Initial Junction Temperature


Fig. 4 - 8/20 μs Pulse Waveform




Fig. 5 - Typical Junction Capacitance





Fig. 6 - Typical Transient Thermal Impedance

PACKAGE OUTLINE DIMENSIONS in inches (millimeters)



Note

- Footprint in accordance with IPC 7351 standard



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Vishay products are not designed for use in life-saving or life-sustaining applications or any application in which the failure of the Vishay product could result in personal injury or death unless specifically qualified in writing by Vishay. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.